

Pneumatic Gripper - Parallel (Side Mount Grip)

Double Acting



KP06MD-M

NITRA Pneumatics grippers are an excellent choice for many automation applications. They are available in both parallel and angular travels in seven different body sizes. Grippers are either double acting, single acting normally closed or single acting normally open. Anodized aluminum bodies include integral mounting slots for position switches.

Features

- Seven sizes available (6 to 40mm bore)
- Double acting or single acting N.O. or N.C.
- Anodized aluminum bodies
- Position switch ready with integral mounting slots



	NITRA Pneumatic Gripper - Parallel (Side Mount Grip) - Double Acting										
Part No.	Description	Style	Action	Size - Bore (mm)	Stroke (mm)	Grip	Body	Port(s)	Price	Weight (lbs)	
KP06MD-M				6	4			Mayor	\$130.00	0.1	
KP10MD-M				10	4			M3 x 0.5	\$140.00	0.2	
KP16MD-M				16	6				\$144.00	0.3	
KP20MD-M	NITRA pneumatic gripper	Parallel	Double acting	20	10	Side mount	Anodized aluminum		\$204.00	0.5	
KP25MD-M				25	14			M5 x 0.8	\$244.00	1.0	
KP32MD-M				32	22]			\$367.00	1.9	
KP40MD-M				40	30]			\$420.00	3.1	

	NITRA Pneumat	ic Gripper Specifications		
Fluid		Air (clean/dry)		
Pressure Range	6mm, 10mm	29 to 101 psig (1.99 to 6.96 bar)		
Tressure manye	16mm to 40mm	22 to 101 psig (1.52 to 6.96 bar)		
Temperature Rang	ge	-4°F to 160°F (-20°C to 60°C)		
Lubrication		Not required		
Panastahility	6mm to 25mm	± 0.01 mm		
Repeatability	32mm to 40mm	± 0.02 mm		
May Fraguency	6mm to 25mm	180 cycles/min		
Max Frequency	32mm to 40mm	60 cycles/min		
Port Size		M3 x 0.5 (6 to 10mm units) M5 x 0.8 (16 to 40mm units)		
Sensor Switch Co.	mpatibility	Nitra CPS9H-xx-x or CPS9C-xx-x		
Includes		Magnet		
Approvals		None		




See <u>www.automationdirect.com</u> for our online Configuration Tool for further selection assistance.


tPNE-254 Pneumatics 1 - 8 0 0 - 6 3 3 - 0 4 0 5




Pneumatic Gripper - Parallel (Side Mount Grip)

Dimensions mm [inches]







	Pneumatic Gripper Dimensions										
Part #	Α	В	С	D	Ε	ØF					
KP06MD-M	53.0 [2.09]	21.0 [0.83]	11.0 [0.43]	8.0 [0.31]	10.5 [0.41]	M3 x 0.5					
KP10MD-M	57.0 [2.24]	30.0 [1.18]	15.5 [0.61]	11.5 [0.45]	16.5 [0.65]	M3 x 0.5					
KP16MD-M	67.5 [2.65]	39.0 [1.54]	21.0 [0.83]	15.0 [0.59]	23.5 [0.93]	M5 x 0.8					
KP20MD-M	84.5 [3.32]	53.0 [2.09]	26.5 [1.04]	16.5 [0.65]	27.5 [1.08]	M5 x 0.8					
KP25MD-M	102.5 [4.04]	71.0 [2.80]	33.5 [1.31]	19.5 [0.77]	33.5 [1.32]	M5 x 0.8					
KP32MD-M	113.0 [4.45]	106.0 [4.17]	48.0 [1.89]	26.0 [1.02]	40.0 [1.57]	M5 x 0.8					
KP40MD-M	139.0 [5.47]	119.0 [4.70]	60.0 [2.36]	30.0 [1.18]	48.0 [1.89]	M5 x 0.8					

See our website www.AutomationDirect.com for complete Engineering drawings.



Pneumatic Gripper - Parallel (Side Mount Grip)

Single Acting - Normally Closed



KP06MSC-M

NITRA Pneumatics grippers are an excellent choice for many automation applications. They are available in both parallel and angular travels in seven different body sizes. Grippers are either double acting, single acting normally closed or single acting normally open. Anodized aluminum bodies include integral mounting slots for position switches.

Features

- Seven sizes available (6 to 40mm bore)
- Double acting or single acting N.O. or N.C.
- Anodized aluminum bodies
- Position switch ready with integral mounting slots



	NITRA Pneumatic Gripper - Parallel (Side Mount Grip) - Single Acting - Normally Closed										
Part No.	Description	Style	Action	Size - Bore (mm)	Stroke (mm)	Grip	Body	Port(s)	Price	Weight (lbs)	
KP06MSC-M				6	4			Mayos	\$130.00	0.1	
KP10MSC-M				10	4			M3 x 0.5 \$140.00	0.2		
KP16MSC-M			Single	16	6			\$144.00	0.3		
KP20MSC-M	NITRA pneumatic gripper	Parallel	acting, normally	20	10	Side mount	Anodized aluminum		\$204.00	0.5	
KP25MSC-M			closed	25	14			M5 x 0.8	\$244.00	1.0	
KP32MSC-M				32	22				\$367.00	1.9	
KP40MSC-M				40	30				\$420.00	3.1	

	NITRA Pneumat	ic Gripper Specifications			
Fluid		Air (clean/dry)			
Drooguro Dongo	6mm, 10mm	50 to 101 psig (3.45 to 6.96 bar)			
Pressure Range	16mm to 40mm	36 to 101 psig (2.48 to 6.96 bar)			
Temperature Rang	ge	-4°F to 160°F (-20°C to 60°C)			
Lubrication		Not required			
Popostability	6mm to 25mm	± 0.01 mm			
Repeatability	32mm to 40mm	± 0.02 mm			
May Eroquanov	6mm to 25mm	180 cycles/min			
Max Frequency	32mm to 40mm	60 cycles/min			
Port Size		M3 x 0.5 (6 to 10mm units) M5 x 0.8 (16 to 40mm units)			
Sensor Switch Co.	mpatibility	Nitra CPS9H-xx-x or CPS9C-xx-x			
Includes		Magnet			
Approvals		None			



See <u>www.automationdirect.com</u> for our online Configuration Tool for further selection assistance.


tPNE-256 Pneumatics 1 - 8 0 0 - 6 3 3 - 0 4 0 5




Pneumatic Gripper - Parallel (Side Mount Grip)

Dimensions

mm [inches]







	Pneumatic Gripper Dimensions										
Part #	A	В	С	D	Ε	ØF					
KP06MSC-M	53.0 [2.09]	21.0 [0.83]	11.0 [0.43]	8.0 [0.31]	10.5 [0.41]	M3 x 0.5					
KP10MSC-M	57.0 [2.24]	30.0 [1.18]	15.5 [0.61]	11.5 [0.45]	16.5 [0.65]	M3 x 0.5					
KP16MSC-M	67.5 [2.65]	39.0 [1.54]	21.0 [0.83]	15.0 [0.59]	23.5 [0.93]	M5 x 0.8					
KP20MSC-M	84.5 [3.32]	53.0 [2.09]	26.5 [1.04]	16.5 [0.65]	27.5 [1.08]	M5 x 0.8					
KP25MSC-M	102.5 [4.04]	71.0 [2.80]	33.5 [1.31]	19.5 [0.77]	33.5 [1.32]	M5 x 0.8					
KP32MSC-M	122.0 [4.80]	106.0 [4.17]	48.0 [1.89]	26.0 [1.02]	40.0 [1.57]	M5 x 0.8					
KP40MSC-M	152.0 [5.98]	119.0 [4.69]	60.0 [2.36]	30.0 [1.18]	48.0 [1.89]	M5 x 0.8					

See our website $\underline{\textit{www.AutomationDirect.com}}$ for complete Engineering drawings.



Pneumatic Gripper - Parallel (Side Mount Grip)

Single Acting - Normally Open



KP06MSA-M

NITRA Pneumatics grippers are an excellent choice for many automation applications. They are available in both parallel and angular travels in seven different body sizes. Grippers are either double acting, single acting normally closed or single acting normally open. Anodized aluminum bodies include integral mounting slots for position switches.

Features

- Seven sizes available (6 to 40mm bore)
- Double acting or single acting N.O. or N.C.
- · Anodized aluminum bodies
- Position switch ready with integral mounting slots



	NITRA Pneumatic Gripper - Parallel (Side Mount Grip) - Single Acting - Normally Open										
Part No.	Description	Style	Action	Size - Bore (mm)	Stroke (mm)	Grip	Body	Port(s)	Price	Weight (lbs)	
KP06MSA-M				6	4			M3 x 0.5	\$130.00	0.1	
KP10MSA-M				10	4			\$140.00	0.2		
KP16MSA-M			Single	16	6			\$144.00	\$144.00	0.3	
KP20MSA-M	NITRA pneumatic gripper	Parallel	acting, normally	20	10	Side mount	Anodized aluminum		\$204.00	0.5	
KP25MSA-M			open	25	14			M5 x 0.8	\$244.00	1.0	
KP32MSA-M				32	22				\$367.00	1.9	
KP40MSA-M				40	30				\$420.00	3.1	

	NITRA Pneumatic Gripper Specifications						
Fluid		Air (clean/dry)					
Dragouro Pongo	6mm, 10mm	50 to 101 psig (3.45 to 6.96 bar)					
Pressure Range	16mm to 40mm	36 to 101 psig (2.48 to 6.96 bar)					
Temperature Ran	ge	-4°F to 160°F (-20°C to 60°C)					
Lubrication		Not required					
Danastahilitu	6mm to 25mm	± 0.01 mm					
Repeatability	32mm to 40mm	± 0.02 mm					
May Eroquanay	6mm to 25mm	180 cycles/min					
Max Frequency	32mm to 40mm	60 cycles/min					
Port Size		M3 x 0.5 (6 to 10mm units) M5 x 0.8 (16 to 40mm units)					
Sensor Switch Co	mpatibility	Nitra CPS9H-xx-x or CPS9C-xx-x					
Includes		Magnet					
Approvals		None					



See <u>www.automationdirect.com</u> for our online Configuration Tool for further selection assistance.


tPNE-258 Pneumatics 1 - 8 0 0 - 6 3 3 - 0 4 0 5





Pneumatic Gripper - Parallel (Side Mount Grip)

Dimensions

mm [inches]







	Pneumatic Gripper Dimensions										
Part #	A	В	С	D	Ε	ØF					
KP06MSA-M	53.0 [2.09]	21.0 [0.83]	11.0 [0.43]	8.0 [0.31]	10.5 [0.41]	M3 x 0.5					
KP10MSA-M	57.0 [2.24]	30.0 [1.18]	15.5 [0.61]	11.5 [0.45]	16.5 [0.65]	M3 x 0.5					
KP16MSA-M	67.5 [2.65]	39.0 [1.54]	21.0 [0.83]	15.0 [0.59]	23.5 [0.93]	M5 x 0.8					
KP20MSA-M	84.5 [3.32]	53.0 [2.09]	26.5 [1.04]	16.5 [0.65]	27.5 [1.08]	M5 x 0.8					
KP25MSA-M	102.5 [4.04]	71.0 [2.80]	33.5 [1.31]	19.5 [0.77]	33.5 [1.32]	M5 x 0.8					
KP32MSA-M	122.0 [4.80]	106.0 [4.17]	48.0 [1.89]	26.0 [1.02]	40.0 [1.57]	M5 x 0.8					
KP40MSA-M	152.0 [5.98]	119.0 [4.69]	60.0 [2.36]	30.0 [1.18]	48.0 [1.89]	M5 x 0.8					

See our website www.AutomationDirect.com for complete Engineering drawings.



Pneumatic Gripper - Parallel (End Mount Grip)

Double Acting



KP06MD-MB

NITRA Pneumatics grippers are an excellent choice for many automation applications. They are available in both parallel and angular travels in seven different body sizes. Grippers are either double acting, single acting normally closed or single acting normally open. Anodized aluminum bodies include integral mounting slots for position switches.

Features

- Seven sizes available (6 to 40mm bore)
- Double acting or single acting N.O. or N.C.
- Anodized aluminum bodies
- Position switch ready with integral mounting slots



	NITRA Pneumatic Gripper - Parallel (End Mount Grip) - Double Acting										
Part No.	Description	Style	Action	Size - Bore (mm)	Stroke (mm)	Grip	Body	Port(s)	Price	Weight (lbs)	
KP06MD-MB	-			6	4			\$130 M3 x 0.5		0.1	
KP10MD-MB				10	4			IVI3 X U.5	\$140.00	0.2	
KP16MD-MB				16	6			\$144.00	0.3		
KP20MD-MB	NITRA pneumatic gripper	Parallel	Double acting	20	10	End mount	Anodized aluminum		\$204.00	0.5	
KP25MD-MB				25	14			M5 x 0.8	\$244.00	1.0	
KP32MD-MB				32	22				\$367.00	1.9	
KP40MD-MB				40	30				\$420.00	3.1	

	NITRA Pneumat	ic Gripper Specifications		
Fluid		Air (clean/dry)		
Drocouro Pongo	6mm, 10mm	29 to 101 psig (1.99 to 6.97 bar)		
Pressure Range	16mm to 40mm	22 to 101 psig (1.52 to 6.97 bar)		
Temperature Ran	ge	-4°F to 160°F (-20°C to 60°C)		
Lubrication		Not required		
Danastahility	6mm to 25mm	± 0.01 mm		
Repeatability	32mm to 40mm	± 0.02 mm		
May Eroquanov	6mm to 25mm	180 cycles/min		
Max Frequency	32mm to 40mm	60 cycles/min		
Port Size		M3 x 0.5 (6 to 10mm units) M5 x 0.8 (16 to 40mm units)		
Sensor Switch Co.	mpatibility	Nitra CPS9H-xx-x or CPS9C-xx-x		
Includes		Magnet		
Approvals		None		



See <u>www.automationdirect.com</u> for our online Configuration Tool for further selection assistance.


tPNE-260 Pneumatics 1 - 8 0 0 - 6 3 3 - 0 4 0 5





Pneumatic Gripper - Parallel (End Mount Grip)

Dimensions

mm [inches]







	Pneumatic Gripper Dimensions										
Part #	A	В	С	D	Ε	ØF					
KP06MD-MB	46.0 [1.81]	21.0 [0.83]	4.0 [0.16]	1.5 [0.06]	10.5 [0.41]	M3 x 0.5					
KP10MD-MB	48.7 [1.92]	30.0 [1.18]	5.5 [0.22]	1.5 [0.06]	16.5 [0.65]	M3 x 0.5					
KP16MD-MB	58.3 [2.30]	39.0 [1.54]	7.5 [0.30]	1.5 [0.06]	23.5 [0.93]	M5 x 0.8					
KP20MD-MB	73.0 [2.87]	53.0 [2.09]	11.5 [0.45]	1.5 [0.06]	27.5 [1.08]	M5 x 0.8					
KP25MD-MB	88.1 [3.47]	71.0 [2.80]	16.0 [0.63]	2.0 [0.08]	33.5 [1.32]	M5 x 0.8					
KP32MD-MB	106.0 [4.17]	106.0 [4.17]	25.0 [0.98]	3.0 [0.12]	40.0 [1.57]	M5 x 0.8					
KP40MD-MB	133.0 [5.24]	132.0 [5.20]	33.0 [1.30]	3.0 [0.12]	48.0 [1.89]	M5 x 0.8					

See our website www.AutomationDirect.com for complete Engineering drawings.



Pneumatic Gripper - Parallel (End Mount Grip)

Single Acting - Normally Closed



KP06MSC-MB

NITRA Pneumatics grippers are an excellent choice for many automation applications. They are available in both parallel and angular travels in seven different body sizes. Grippers are either double acting, single acting normally closed or single acting normally open. Anodized aluminum bodies include integral mounting slots for position switches.

Features

- Seven sizes available (6 to 40mm bore)
- Double acting or single acting N.O. or N.C.
- Anodized aluminum bodies
- Position switch ready with integral mounting slots



	NITRA Pneumatic Gripper - Parallel (End Mount Grip) - Single Acting Normally Closed										
Part No.	Description	Style	Action	Size - Bore (mm)	Stroke (mm)	Grip	Body	Port(s)	Price	Weight (lbs)	
KP06MSC-MB		Parallel	Single acting, normally closed	6	4	End Mount	Anodized aluminum	M3 x 0.5	\$130.00	0.1	
KP10MSC-MB	NITRA pneumatic gripper			10	4				\$140.00	0.2	
KP16MSC-MB				16	6			M5 x 0.8	\$144.00	0.3	
KP20MSC-MB				20	10				\$204.00	0.5	
KP25MSC-MB				25	14				\$244.00	1.0	
KP32MSC-MB				32	22				\$367.00	1.9	
KP40MSC-MB				40	30				\$420.00	3.1	

NITRA Pneumatic Gripper Specifications						
Fluid		Air (clean/dry)				
Виссения Вамия	6mm, 10mm	50 to 101 psig (3.45 to 6.96 bar)				
Pressure Range	16mm to 40mm	36 to 101 psig (2.48 to 6.96 bar)				
Temperature Ran	ge	-4°F to 160°F (-20°C to 60°C)				
Lubrication		Not required				
Repeatability	6mm to 25mm	± 0.01 mm				
	32mm to 40mm	± 0.02 mm				
May Eroquanay	6mm to 25mm	180 cycles/min				
Max Frequency	32mm to 40mm	60 cycles/min				
Port Size		M3 x 0.5 (6 to 10mm units) M5 x 0.8 (16 to 40mm units)				
Sensor Switch Compatibility		Nitra CPS9H-xx-x or CPS9C-xx-x				
Includes		Magnet				
Approvals		None				



See <u>www.automationdirect.com</u> for our online Configuration Tool for further selection assistance.


tPNE-262 Pneumatics 1 - 8 0 0 - 6 3 3 - 0 4 0 5





Pneumatic Gripper - Parallel (End Mount Grip)

Dimensions

mm [inches]







Pneumatic Gripper Dimensions										
Part #	A	В	С	D	Ε	ØF				
KP06MSC-MB	46.0 [1.81]	21.0 [0.83]	4.0 [0.16]	1.5 [0.06]	10.5 [0.41]	M3 x 0.5				
KP10MSC-MB	48.7 [1.92]	30.0 [1.18]	5.5 [0.22]	1.5 [0.06]	16.5 [0.65]	M3 x 0.5				
KP16MSC-MB	58.3 [2.30]	39.0 [1.54]	7.5 [0.30]	1.5 [0.06]	23.5 [0.93]	M5 x 0.8				
KP20MSC-MB	73.0 [2.87]	53.0 [2.09]	11.5 [0.45]	1.5 [0.06]	27.5 [1.08]	M5 x 0.8				
KP25MSC-MB	88.1 [3.47]	71.0 [2.80]	16.0 [0.63]	2.0 [0.08]	33.5 [1.32]	M5 x 0.8				
KP32MSC-MB	106.0 [4.17]	106.0 [4.17]	25.0 [0.98]	3.0 [0.12]	40.0 [1.57]	M5 x 0.8				
KP40MSC-MB	133.0 [5.24]	132.0 [5.20]	33.0 [1.30]	3.0 [0.12]	48.0 [1.89]	M5 x 0.8				

See our website $\underline{\textit{www.AutomationDirect.com}}$ for complete Engineering drawings.



Pneumatic Gripper - Parallel (End Mount Grip)

Single Acting - Normally Open



KP06MSA-MB

NITRA Pneumatics grippers are an excellent choice for many automation applications. They are available in both parallel and angular travels in seven different body sizes. Grippers are either double acting, single acting normally closed or single acting normally open. Anodized aluminum bodies include integral mounting slots for position switches.

Features

- Seven sizes available (6 to 40mm bore)
- Double acting or single acting N.O. or N.C.
- Anodized aluminum bodies
- Position switch ready with integral mounting slots



	NITRA Pneumatic Gripper - Parallel (End Mount Grip) - Single Acting Normally Open										
Part No.	Description	Style	Action	Size - Bore (mm)	Stroke (mm)	Grip	Body	Port(s)	Price	Weight (lbs)	
KP06MSA-MB	NITRA pneumatic gripper	Parallel	Single acting, normally open	6	4	End Mount	Anodized aluminum	M3 x 0.5	\$130.00	0.1	
KP10MSA-MB				10	4				\$140.00	0.2	
KP16MSA-MB				16	6			M5 x 0.8	\$144.00	0.3	
KP20MSA-MB				20	10				\$204.00	0.5	
KP25MSA-MB				25	14				\$244.00	1.0	
KP32MSA-MB				32	22				\$367.00	1.9	
KP40MSA-MB				40	30				\$420.00	3.1	

NITRA Pneumatic Gripper Specifications						
Fluid		Air (clean/dry)				
Bracoura Banga	6mm, 10mm	50 to 101 psig (3.45 to 6.96 bar)				
Pressure Range	16mm to 40mm	36 to 101 psig (2.48 to 6.96 bar)				
Temperature Ran	ge	-4°F to 160°F (0°C to 60°C)				
Lubrication		Not required				
Repeatability	6mm to 25mm	± 0.01 mm				
	32mm to 40mm	± 0.02 mm				
Max Frequency	6mm to 25mm	180 cycles/min				
	32mm to 40mm	60 cycles/min				
Port Size		M3 x 0.5 (6 to 10mm units) M5 x 0.8 (16 to 40mm units)				
Sensor Switch Compatibility		Nitra CPS9H-xx-x or CPS9C-xx-x				
Includes		Magnet				
Approvals		None				



See <u>www.automationdirect.com</u> for our online Configuration Tool for further selection assistance.


tPNE-264 Pneumatics 1 - 8 0 0 - 6 3 3 - 0 4 0 5





Pneumatic Gripper - Parallel (End Mount Grip)

Dimensions

mm [inches]







Pneumatic Gripper Dimensions										
Part #	A	В	С	D	E	ØF				
KP06MSA-MB	46.0 [1.81]	21.0 [0.83]	4.0 [0.16]	1.5 [0.06]	10.5 [0.41]	M3 x 0.5				
KP10MSA-MB	48.7 [1.92]	30.0 [1.18]	5.5 [0.22]	1.5 [0.06]	16.5 [0.65]	M3 x 0.5				
KP16MSA-MB	58.3 [2.30]	39.0 [1.54]	7.5 [0.30]	1.5 [0.06]	23.5 [0.93]	M5 x 0.8				
KP20MSA-MB	73.0 [2.87]	53.0 [2.09]	11.5 [0.45]	1.5 [0.06]	27.5 [1.08]	M5 x 0.8				
KP25MSA-MB	88.1 [3.47]	71.0 [2.80]	16.0 [0.63]	2.0 [0.08]	33.5 [1.32]	M5 x 0.8				
KP32MSA-MB	106.0 [4.17]	106.0 [4.17]	25.0 [0.98]	3.0 [0.12]	40.0 [1.57]	M5 x 0.8				
KP40MSA-MB	133.0 [5.24]	132.0 [5.20]	33.0 [1.30]	3.0 [0.12]	48.0 [1.89]	M5 x 0.8				

See our website $\underline{\textit{www.AutomationDirect.com}}$ for complete Engineering drawings.