



Pliers & Cutting Tools

Locking Pliers

CHANNELLOCK® Locking Pliers make fast work of your toughest jobs. Available in curved jaw for gripping fasteners and round stock, or long nose for maximum clearance in confined work environments. An extended-release lever allows for quick one-handed control and prevents finger pinch, while forged steel jaws and a centered steel rod and lever ensure strength and tight handle alignment. CHANNELLOCK Locking Pliers feature an epoxy resin coating for ultimate rust prevention and spatter resistance.



Features

- Curved jaw provides additional contact points on fasteners and round stock
- Long nose design offers maximum clearance in tight spaces
- Extended-release lever allows quick, one-handed control and prevents finger pinch
- Epoxy resin coating provides rust prevention and spatter resistance



CURVED JAW
offers advanced control, providing additional contact points on multiple fastener types and round stock



LONG NOSE
for maximum clearance in confined work environments



Locking Pliers							
Part Number	Part Image	Pliers Type	Overall Length	Jaw Length	Jaw Capacity	Jaw Thickness	Price
102-5		Curved Jaw	5.6in [141mm]	0.91in [23.0mm]	1.26in [32.0mm]	0.59in [15.0mm]	\$19.50
102-7		Curved Jaw	7.5in [191mm]	1.30in [33.0mm]	1.65in [42.0mm]	0.79in [20.0mm]	\$23.50
102-10		Curved Jaw	9.4in [240mm]	1.61in [41.0mm]	2.48in [63.0mm]	0.51in [13.0mm]	\$28.00
103-6		Long Nose	7.0in [177mm]	2.05in [52.0mm]	2.17in [55.0mm]	0.59in [15.0mm]	\$21.00
103-10		Long Nose	9.1in [232mm]	2.56in [65.0mm]	2.76in [70.0mm]	0.45in [11.4mm]	\$26.00