



# Check Valves

CITO check valves are great general purpose valves which allow flow in only one direction.



**Part No. CV-1202-MF**

*Note: Included nipple shown installed*

## Features

- Durable brass bodies with female NPT threads
- Temperature rating: 20-250°F [7-121°C]
- Pressure rating: 2-100 psi
- Includes a matching thread close nipple
- Works with many fluids
- Viton O-rings
- Made in USA



See [www.AutomationDirect.com](http://www.AutomationDirect.com) for a wide variety of fitting options

Check Valves				
Part Number	Description	Drawing Link	Weight (lb)	Price
<u><a href="#">CV-1202-MF</a></u>	CITO pneumatic, coolant, oil or water threaded fitting, female, check valve, brass body, brass threads, (2) 1/4in female NPT.	<a href="#">PDF</a>	0.25	\$28.00
<u><a href="#">CV-1203-MF</a></u>	CITO pneumatic, coolant, oil or water threaded fitting, female, check valve, brass body, brass threads, (2) 3/8in female NPT.	<a href="#">PDF</a>	0.30	\$34.00
<u><a href="#">CV-1204-MF</a></u>	CITO pneumatic, coolant, oil or water threaded fitting, female, check valve, brass body, brass threads, (2) 1/2in female NPT.	<a href="#">PDF</a>	0.35	\$42.00



# Valves and Accessories

## Overview

StackFlow™ product line from CITO Products offers a robust series of modular process valves. Body sections can stack together to form a valve bank assembly with common inlets at each end and outlets discharging at the bottom of the assembly. Distribution block, manual ball valve and solenoid diaphragm valve models are available and can all be mixed in the same assembly.


## Features

- High flow capacity glass-filled nylon bodies
- Integral flow indicator available on some models
- 24 VAC/DC and 120VAC solenoids
- Cleanable inlet screens allow operation in tough environments
- Pressure and temperature gauges available
- Working fluids: water, coolant, oils
- Made in USA



See [www.AutomationDirect.com](http://www.AutomationDirect.com) for a wide variety of fitting options

## Assembly Example



For detailed assembly and configuration details, click or scan the QR code for our downloadable assembly instructions

