



Flow Indicators

CITO flow indicators use a molded turbine to indicate when fluid is flowing. They are a useful addition to many piping systems.



Part No. [MF-0404-N](#)

Features

- 1/4" to 1" NPT threaded connections
- Smaller bodies are anodized aluminum. Larger bodies are glass-filled nylon
- Intended for use with water, coolant and oil. Use with air/gas could damage the turbine
- Made in USA



Part No. [RFH-0808](#)



See www.AutomationDirect.com for a wide variety of fitting options

Flow Indicators							
Part Number	Description	Temperature	Pressure (psi)	Flow (gpm)	Drawing Link	Weight (lb)	Price
MF-0404-N	CITO MiniFlow flow indicator, 0.1-6.5 GPM, 1/4in NPT thread, anodized aluminum.	20-210°F [-6.7-98.9°C]	1-125	0.1-6.5	PDF	0.43	\$124.00
MF-0606-N	CITO MiniFlow flow indicator, 0.1-7 GPM, 3/8in NPT thread, anodized aluminum.			0.1-7.0	PDF	0.42	\$124.00
RFH-0808	CITO RotoFlow flow indicator, 1-22 GPM, 1/2in NPT thread, glass-filled nylon.	20-160°F [-6.7-71.1°C]	1-100	1.0-22.0	PDF	1.31	\$184.00
RFH-1212	CITO RotoFlow flow indicator, 1-40 GPM, 3/4in NPT thread, glass-filled nylon.			1.0-40.0	PDF	1.29	\$184.00
RFH-1616	CITO RotoFlow flow indicator, 1-60 GPM, 1in NPT thread, glass-filled nylon.			1.0-60.0	PDF	1.23	\$184.00



Valves and Accessories

Overview

StackFlow™ product line from CITO Products offers a robust series of modular process valves. Body sections can stack together to form a valve bank assembly with common inlets at each end and outlets discharging at the bottom of the assembly. Distribution block, manual ball valve and solenoid diaphragm valve models are available and can all be mixed in the same assembly.


Features

- High flow capacity glass-filled nylon bodies
- Integral flow indicator available on some models
- 24 VAC/DC and 120VAC solenoids
- Cleanable inlet screens allow operation in tough environments
- Pressure and temperature gauges available
- Working fluids: water, coolant, oils
- Made in USA



See www.AutomationDirect.com for a wide variety of fitting options

Assembly Example



For detailed assembly and configuration details, click or scan the QR code for our downloadable assembly instructions

