

CT Series NEMA 3R Double-Door Hinge Cover



Applications

Designed as a housing for current and voltage transformers, recorders, meters, relays and/or for terminal instrumentation. Can also be used as a service or junction box.



Construction

- Manufactured from 14 and 12 gauge carbon steel
- Fully seam welded and ground smooth, with weep hole
- Drip shield
- Lift-off hinges, gasketed doors
- Supplied with non-locking "T" handle
- Meter seal provisions
- Mounting holes in back provided
- Supplied with studs in back of enclosure to support optional wood subpanel [available from Wiegmann]
- Uses WA8 handle

Finish

- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces

Listings

- UL Listed Type 3R [UL file E23553]



Shipping Schedule				
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days

Color indicates shipping lead time in business days.

CT Series NEMA 3R Double-Door Hinge Cover			
Part Number	Price	Body/Door Steel Gauge	Enclosure Size HxWxD
CTDD302410	\$594.00	14/14	24.38 x 30.42 x 10.06 [619 x 773 x 256]
CTDD303012	\$667.00	12/12	30.37 x 30.46 x 12.08 [771 x 774 x 314]
CTDD303612	\$743.00		36.37 x 30.46 x 12.08 [924 x 772 x 307]
CTDD362412	\$633.00	14/14	24.38 x 36.42 x 12.06 [619 x 925 x 306]
CTDD363012	\$719.00	12/12	30.37 x 36.46 x 12.08 [771 x 926 x 307]
CTDD363212	\$738.00		32.37 x 36.46 x 12.08 [822 x 926 x 307]
CTDD363612	\$868.00		36.37 x 36.46 x 12.06 [924 x 926 x 306]
CTDD363616	\$901.00		36.37 x 36.46 x 16.08 [924 x 926 x 408]
CTDD424212	\$949.00		42.37 x 42.46 x 12.08 [1076 x 1078 x 307]
CTDD443012	\$705.00		30.37 x 44.46 x 12.08 [771 x 1129 x 307]
CTDD484816	\$1,119.00		48.37 x 48.46 x 16.08 [1229 x 1231 x 408]

Notes: Dimensions in inches [millimeters].
Letters in table correspond to letters on dimensional drawings.

Dimensions

