

.7518NT3FVD56C-S Cut Sheet



WEG Electric S premium efficiency AC induction motor, high-performance inverter duty, 3/4hp, 3-phase, 230/460 VAC, 1800rpm, TENV, 56CZ frame, rolled steel, C-face/rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/.7518NT3FVD56C-S>

Technical Specifications

Brand	WEG Electric
Item	Motor
Series	S
Efficiency Group	Premium efficiency
Efficiency	81.5
Voltage Type	AC
Motor Type	Induction
Motor Application	High-performance inverter duty
Horsepower Rating	3/4hp
Number of Phases	3
Voltage Rating	230/460 VAC
Synchronous Speed	1800rpm
Nameplate RPM	1770rpm
Overload Type	None
Enclosure Type	TENV

Shaft Type	Round with square key
Shaft Diameter	5/8in
Shaft Material	1045 carbon steel
Motor Frame	56CZ
Frame Material	Rolled steel
Electrically Reversible	Yes
Insulation Class	Class F
IP Rating	IP55
Constant Torque Rating	1000:1
Variable Torque Rating	1000:1
Service Factor	1.0
Integrated Brake	No
Junction Box Orientation	F1
Mounting	C-face/rigid base
Mounting Orientation	Horizontal or vertical

Agency Approvals

UL Listed File #	E104590
CE	None
CSA File #	LR38324
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/.7518NT3FVD56C-S.pdf>
See store item page for other formats.