



# Avtron Encoder Kit

## HS35A Encoder Kit Overview

Avtron™ HS35A Encoder kits come standard on US MOTORS ACCU-Torq® series encoder motors or can be purchased separately for installation on existing dual shaft motors such as Marathon Black Max. The HS35A encoders fit shafts from 1/2" to 1" easily, using durable shaft inserts. The encoders can be adapted to different shaft sizes by replacing or removing the included inserts, enabling customer stockrooms to swiftly meet any need. The shaft inserts and insulated bearings also provide isolation from motor shaft currents, while permitting case grounding to meet NEC requirements. Avtron encoders have superior shaft seals and bearings that stay sealed to keep out contamination caused by temperature cycling and liquid sprays. Encoder seals are protected by mechanical barriers to prevent flexing or failure, and Avtron's rugged bearings feature synthetic lubricants for even longer life. Avtron uses only unbreakable disks and a sensor-to-disk gap over eight times larger than the competition. The optical HS35A encoders use superior sensor, disk, bearing, and seal technology to give top performance in industrial conditions.



**HS35AY1CDU1EA000**

## HS35A Features

- All digital, fully integrated design
- Easily mountable on US MOTORS ACCU-Torq series or Marathon Black Max Series vector duty motors
- No mechanical adjustments or trim potentiometers
- Innovative shaft ring retains collar during installation
- Advanced sensor technology
- Superior bearings with synthetic lubricant for longer life
- Encoder provides signal complements and marker pulse (A,A-, B,B-, Z,Z-)
- Insulated from motor shaft currents
- Models can be resized by interchanging inserts
- Included basket guard adds even more protection

### HS35A Encoder Specifications

<b>Part Number</b>	HS35AY1CDU1EA000
<b>Price</b>	\$839.00
<b>Operating Power</b>	Volts: 5-28 VDC Current: 50 mA, no load
<b>Output Format</b>	A Quad B with marker (A,/A, B,/B, Z,/Z)
<b>Frequency Range</b>	0 to 125 kHz
<b>PPR</b>	1024
<b>Max Speed</b>	6000 RPM
<b>Temperature</b>	-20° to 100°C*
<b>Environmental</b>	IP65
<b>Vibration</b>	5-2000 Hz
<b>Shock</b>	50G, 11ms duration
<b>Weight</b>	1.6 lbs [730g]
<b>Drawing Link</b>	<a href="#">PDF</a>

\*Consult Avtron for temperature/speed derating:  
<https://www.nidec-avtronencoders.com/contact>



Click image above for Encoder Installation:

<https://www.youtube.com/watch?v=ZhX63xp7kOw>



# ACCU-Torq® Vector Duty 3-Phase AC Motors

## 56C – 256TC Frame – 1/4hp to 20hp

### Available with or without encoder installed

U.S. MOTORS® ACCU-Torq® series AC motors offer a solution to applications requiring accurate positioning or precise speed control without the rapid acceleration dynamics of a servomotor. ACCU-Torq motors are designed to be used with AC drives, including full closed-loop vector drives, in applications requiring up to a 5000:1 constant torque speed range.

### Standard Features

- 230/460 VAC
- Rated output: 1/4 - 20hp
- 1800 rpm, with or without encoder
- 1200 rpm up to 10hp
- Encoder Motors are pre-built with Avtron HS35A encoders. Complete encoder kit is also available for separate purchase.
- Standard motors have dual shaft for encoder mounting.
- Class F insulation (155° C), inverter duty NEMA MG1 Part 31
- Constant torque operation; zero to base speed on vector drives
- Constant horsepower operation to twice base speed
- Optimized for operation with IGBT and intelligent power module drives (NEMA®+ Design A)
- F-1 Standard, field convertible to F-2 for 180 frame and above
- Normally closed thermostats standard
- Horizontal or Vertical mounting
- Continuous duty at 40°C ambient

### Applications

- Packaging machinery
- Extruders
- Material handling
- Indexing and positioning
- Positive displacement pumps
- DC Motor Replacements



**UN5T2BC**



**UN5T2BC-HS35A**



Cover can be removed to reveal second shaft



**HS35AY1CDU1EA000**



# ACCU-Torq® Vector Duty 3-Phase AC Motors

Motor Specifications – 3-phase												
Part Number	Price	HP*	Base RPM	Volts	Enclosure	Encoder Included	NEMA Frame	Service Factor	NEMA Design	Weight (lb)	Data Pack Links*	Drawing Links
<b>Rigid Base With C-face - 1800 RPM</b>												
<a href="#">UN14T2BC</a>	\$370.00	1/4	1800	230/460 VAC	TENV	No	56C	1.0	A	35	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN14T2BC-HS35A</a>	\$1,199.00					Yes				30	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN12T2BC</a>	\$448.00	1/2				No				42	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN12T2BC-HS35A</a>	\$1,298.00					Yes				30	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN1T2BFC</a>	\$530.00	1				No	56C			43	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN1T2BFC-HS35A</a>	\$1,379.00					Yes	30			<a href="#">PDF</a>	<a href="#">PDF</a>	
<a href="#">UN1T2BC</a>	\$530.00					No	143TC			43	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN1T2BC-HS35A</a>	\$1,379.00					Yes	30			<a href="#">PDF</a>	<a href="#">PDF</a>	
<a href="#">UN32T2BC</a>	\$651.00	1 1/2				No	145TC			50	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN32T2BC-HS35A</a>	\$1,498.00					Yes				35	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN2T2BC</a>	\$697.00	2				No	145TC			57	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN2T2BC-HS35A</a>	\$1,538.00					Yes				60	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN3T2BC</a>	\$781.00	3				No	182TC			65	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN3T2BC-HS35A</a>	\$1,625.00					Yes				60	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN5T2BC</a>	\$908.00	5				No	184TC			85	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN5T2BC-HS35A</a>	\$1,738.00					Yes				60	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN7T2BC</a>	\$1,241.00	7 1/2				No	213TC			135	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN7T2BC-HS35A</a>	\$2,071.00					Yes				105	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN10T2BC</a>	\$1,499.00	10				No	215TC			178	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN10T2BC-HS35A</a>	\$2,329.00					Yes				120	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN15T2BC</a>	\$2,070.00	15	No	254TC	255	<a href="#">PDF</a>	<a href="#">PDF</a>					
<a href="#">UN15T2BC-HS35A</a>	\$2,900.00		Yes		120	<a href="#">PDF</a>	<a href="#">PDF</a>					
<a href="#">UN20T2BC</a>	\$2,551.00	20	No	256TC	266	<a href="#">PDF</a>	<a href="#">PDF</a>					
<a href="#">UN20T2BC-HS35A</a>	\$3,381.00		Yes		230	<a href="#">PDF</a>	<a href="#">PDF</a>					
<b>Rigid Base With C-face - 1200 RPM</b>												
<a href="#">UN1T3BC</a>	\$578.00	1	1200	230/460 VAC	TENV	No	145TC	1.0	A	35	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN2T3BC</a>	\$963.00	2					184TC			75	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN5T3BC</a>	\$1,707.00	5					215TC			60	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN7T3BC</a>	\$2,279.00	7 1/2					254TC			211	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">UN10T3BC</a>	\$2,752.00	10					256TC			266	<a href="#">PDF</a>	<a href="#">PDF</a>

\*See Motor Data Pack for additional specifications



# ACCU-Torq® Vector Duty 3-Phase AC Motors

Performance Data – 3-phase																	
Part Number	HP*	Full Load RPM*	Volts*	Current (230V/460V)			Torque			Resistance Main		Torque Speed Rating		Full Load Effic. %	Full Load Power Factor	Moment of Inertia (lb-ft <sup>2</sup> )	
				No Load Current	Full Load Amps	Locked Rotor Amps	Full Load (lb-ft)	Locked Rotor	Break-down			Constant	Variable				
										% of Full Load Torque	230V						460V
<b>Rigid Base With C-face - 1800 RPM</b>																	
<a href="#">UN14T2BC</a>	1/4	1765	230/460 VAC	0.8 / 0.4	1 / 0.5	8.2 / 4.1	0.70	419	586	12.42	49.69	5000:1	5000:1	77.0	61.1	0.070	
<a href="#">UN14T2BC-HS35A</a>					1 / 0.5						49.69						
<a href="#">UN12T2BC</a>	1/2	1750		1 / 0.5	1.5 / 0.8	12.1 / 6	1.50	335	457	6.47	25.87			84.0	69.5	74.2	0.105
<a href="#">UN12T2BC-HS35A</a>					1.5 / 0.8						25.87						
<a href="#">UN1T2BC</a>	1	1755		2.2 / 1.1	3.2 / 1.6	32 / 15.8	3.00	480	606	2.72	10.88			86.5	69.7	0.14	
<a href="#">UN1T2BC-HS35A</a>											3.2 / 1.6						10.88
<a href="#">UN1T2BFC</a>					3.2 / 1.6	31 / 15.6	476	600	2.66	10.64							
<a href="#">UN1T2BFC-HS35A</a>										10.64							
<a href="#">UN32T2BC</a>	1 1/2	1760		3.2 / 1.6	4.6 / 2.3	52 / 25.9	4.50	518	665	1.55	6.18			87.5	63.6	0.314	
<a href="#">UN32T2BC-HS35A</a>					4.6 / 2.3						6.18						
<a href="#">UN2T2BC</a>	2	1750		3.3 / 1.7	5.6 / 2.8	56 / 28	6.00	425	543	1.37	5.46			90.2	74.5	0.472	
<a href="#">UN2T2BC-HS35A</a>					5.6 / 2.8						5.46						
<a href="#">UN3T2BC</a>	3	1770		7.9 / 4	10.1 / 5	92 / 46	8.90	400	573	0.77	3.08			92.4	80.7	0.964	
<a href="#">UN3T2BC-HS35A</a>					10.1 / 5						3.08						
<a href="#">UN5T2BC</a>					5	1775	8 / 4	14.2 / 7.1	139 / 70	14.80	363						522
<a href="#">UN5T2BC-HS35A</a>	14.2 / 7.1	1.84															
<a href="#">UN7T2BC</a>	7 1/2	1775		9 / 4.5	18.8 / 9.4	178 / 89	22.20	349	445	0.21	0.84			94.5	83.4	3.43	
<a href="#">UN7T2BC-HS35A</a>			18.8 / 9.4		0.84												
<a href="#">UN10T2BC</a>	10	1785	12.9 / 6.4	25.3 / 12.7	275 / 138	29.60	416	519	0.13	0.53	94.1	80.3	3.56				
<a href="#">UN10T2BC-HS35A</a>				25 / 12.7						0.53							
<a href="#">UN15T2BC</a>	15	1780	14.3 / 7.2	36 / 17.8	345 / 172	44.20	394	381	0.08	0.33							
<a href="#">UN15T2BC-HS35A</a>				36 / 17.8						0.33							
<a href="#">UN20T2BC</a>	20	1780	22.9 / 11.5	50 / 24.8	486 / 243	58.90	419	403	0.06	0.24							
<a href="#">UN20T2BC-HS35A</a>				50 / 24.8						0.24							
<b>Rigid Base With C-face - 1200 RPM</b>																	
<a href="#">UN1T3BC</a>	1	1150	230/460 VAC	7.1	3.7 / 1.8	21.1 / 10.5	4.60	298	390	3.59	14.35	5000:1	5000:1	80.0	63.8	0.122	
<a href="#">UN2T3BC</a>	2	1170		2.1 / 4.3	6.2 / 3.1	47.3 / 23.5	9.00	228	386	1.79	7.17			86.5	69.4	0.361	
<a href="#">UN5T3BC</a>	5	1175		10.9 / 5.5	15.9 / 7.9	127.7 / 63.9	22.30	383	445	0.35	1.42			89.5	65.9	0.928	
<a href="#">UN7T3BC</a>	7 1/2	1185		10.5 / 5.3	19.8 / 9.9	162.7 / 81.4	33.20	285	393	0.27	1.08			91.7	77.4	3.21	
<a href="#">UN10T3BC</a>	10			11.9 / 6	25 / 12.7	199.8 / 99.9	45.00	269	366	0.20	0.79			92.4	80.1	4.05	

\*See Motor Data Pack for additional specifications linked in specification table above