

018700-30 Cut Sheet



Stego Filter Fan Plus FPI intake fan, side mount, 11 CFM, 230 VAC operating voltage, G3 (coarse) filter mat, NEMA 12, indoor use only, 3.62 x 3.62in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018700-30>

Technical Specifications

| | |
|---|------------------------|
| Brand | Stego |
| Series | Filter Fan Plus FPI |
| Airflow Direction | Intake |
| Item | Fan |
| Mounting | Side |
| With Air Flaps | No |
| Filter Media | G3 (coarse) filter mat |
| Free Airflow | 11 CFM |
| Airflow with Grill and Filter(s) | 7.7 CFM |
| Operating Voltage | 230 VAC |
| Frequency | 60 Hz |
| Power Consumption | 12W |
| Current Draw | 52 mA |

| | |
|--------------------------------|--|
| Electrical Connection | (2) AWG 22 x 11.8in long wires |
| Maximum Static Pressure | 42Pa |
| Operating Temperature | -4 to 158 deg F |
| Average Noise Level | 39 dBA |
| NEMA Rating | 12 |
| Application | Indoor use only |
| IP Rating | IP54 |
| Enclosure Cutout | 3.62 x 3.62in |
| Color | RAL 7035 light gray |
| Includes | Optional mounting screws |
| Additional Information | Purchase exhaust grille separately. Fan will also safely operate at 50Hz, but with reduced airflow. Contact manufacturer for 50Hz performance data |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E234324 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |