

# 018722-30 Cut Sheet



Stego Filter Fan Plus FPI intake fan, side mount, 105 CFM, 24 VDC operating voltage, G3 (coarse) filter mat, NEMA 12, indoor use only, 6.93 x 6.93in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018722-30>

## Technical Specifications

<b>Brand</b>	Stego	<b>Electrical Connection</b>	3-pole clamp for AWG 14 wire, 7.1 in-lb maximum clamping torque
<b>Series</b>	Filter Fan Plus FPI	<b>Maximum Static Pressure</b>	125Pa
<b>Airflow Direction</b>	Intake	<b>Operating Temperature</b>	-13 to 158 deg F
<b>Item</b>	Fan	<b>Average Noise Level</b>	63 dBA
<b>Mounting</b>	Side	<b>NEMA Rating</b>	12
<b>With Air Flaps</b>	No	<b>Application</b>	Indoor use only
<b>Filter Media</b>	G3 (coarse) filter mat	<b>IP Rating</b>	IP54
<b>Free Airflow</b>	105 CFM	<b>Enclosure Cutout</b>	6.93 x 6.93in
<b>Airflow with Grill and Filter(s)</b>	92 CFM	<b>Color</b>	RAL 7035 light gray
<b>Operating Voltage</b>	24 VDC	<b>Includes</b>	Optional mounting screws
<b>Power Consumption</b>	12W	<b>Additional Information</b>	Purchase exhaust grille separately
<b>Current Draw</b>	500 mA		

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>