


BX-16TDY2 Sourcing 12–24 VDC Output Module



Terminal Blocks
Sold Separately

Discrete Output Specifications

Output Type	Sourcing
Outputs per Module	16
Commons (Isolated)	4
Points per Common	4
Maximum Current per Common	4A
Nominal Voltage Range*	12–24 VDC
Operating Voltage Range*	5–36 VDC
Maximum Voltage	36 VDC
Minimum Output Current	0.1 mA @ 24 VDC
Maximum Output (Load) Current	1A/point, no derating
Maximum Inrush Current	10A for 50ms
Maximum Leakage Current	1µA
ON Voltage Drop	0.1 V max
OFF-ON Response	< 10ms
ON-OFF Response	< 10ms
Overcurrent Protection	N/A
Fuse Type	User-supplied external fuse
* Class 2 or LPS Power Supply required.	

BX-16TDY2 \$99.00

Output Module 16-pt,
12–24 VDC Sourcing,
1A/point

We recommend using prewired ZIPLink cables and connection modules.


If you wish to hand-wire your module, a removable terminal block is available. See Wiring Solutions section for all options.



Module Specifications

Heat Dissipation	6.5 W Max
Backplane Power Consumption	0.5 W Max
Status Indicators	Logic Side, Green
Weight	91g [3.2 oz]
Software Version Required	Do-more! Designer v2.11 or later

Discrete Output Wiring Diagram



IMPORTANT!



Hot-Swapping Information

Note: This device cannot be Hot Swapped.

BRX Discrete Expansion Modules

Overview


One of the unique features of the BRX platform is its ability to expand its capability to fit your application solution. One of the ways the BRX platform can do this is by using expansion modules that conveniently "snap on" to the side of any BRX MPU. Once the expansion module has been snapped in place and is added to the project, it instantly adds I/O to the MPU with little to no additional setup required.

The expansion modules give you the ability to add discrete I/O as needed and are identified as an input module, output module or combination input/output module. On the front panel of the discrete I/O

expansion modules, a color scheme and a symbol are used to denote the module type.

Most modules are available in 5, 8, 12 or 16 point variations consisting of sink/source DC inputs/outputs, AC inputs/outputs, relay outputs and combination modules. Some are available with 32 points.

The modules ship without wiring terminals. This allows you to select the termination style that best fits your application. Several wiring options are available, including screw terminal connectors, spring clamp terminal connectors and pre-wired **ZIP**Link cable solutions.



Hot-Swapping Information

Note: This device cannot be Hot Swapped.


General Specifications

All BRX discrete expansion modules have the same general specifications listed in the table below.

General Specifications	
Operating Temperature	0° to 60°C [32° to 140°F]
Storage Temperature	-20° to 85°C [-4° to 185°F]
Humidity	5 to 95% (non-condensing)
Environmental Air	No corrosive gases permitted
Vibration	IEC60068-2-6 (Test Fc)
Shock	IEC60068-2-27 (Test Ea)
Enclosure Type	Open Equipment
Noise Immunity	NEMA ICS3-304
EU Directive	See the "EU Directive" topic in the Help File
Agency Approvals	UL 61010-2 - UL File # E185989 Canada and USA CE Compliant EN61131-2*

* Meets EMC and Safety requirements. See D.O.C. for details.

Dimensions, inches[mm]




NOTE: When removing an expansion module, make sure there is room for the module to slide away from the system. Failure to do so will result in difficulty in removing the module.

BRX Discrete Expansion Modules

Discrete Input Modules

Fourteen (14) discrete input modules are available in various DC and AC voltage ranges. Input module faceplates have a blue terminal bar and symbol  for easy distinction from other module types.




Discrete Input Modules

Part Number	Points	Input Type	Price
BX-08NF3	8	3–5 VDC, Sinking/Sourcing/TTL	\$51.00
BX-08ND3		12–24 VDC, Sinking/Sourcing	\$52.00
BX-08NB		12–24 VAC	\$52.00
BX-08NA		120–240 VAC	\$56.00
BX-08SIM		Simulator	\$68.00
BX-12ND3	12	12–24 VDC, Sinking/Sourcing	\$69.00
BX-12NB		12–24 VAC	\$54.00
BX-12NA		120–240 VAC	\$73.00
BX-16NF3	16	2–5 VDC, Sinking/Sourcing/TTL	\$73.00
BX-16ND3		12–24 VDC, Sinking/Sourcing	\$75.00
BX-16NB		12–24 VAC	\$65.00
BX-16NA		120–240 VAC	\$81.00
BX-16NN	16	48 VDC, Sinking/Sourcing	\$83.00
BX-32ND3		12–24 VDC, Sinking/Sourcing	\$148.00

Discrete Output Modules

Twenty-one (21) discrete output modules are available in DC sinking, DC sourcing, AC voltage and Relay type outputs. Output module faceplates have a red terminal bar and symbol  for easy distinction from other module types.




Discrete Output Modules

Part Number	Points	Output Type	Price
BX-05TRS	5	Relay Form C (SPDT)	\$73.00
BX-05TRS-1		Relay Form C (SPDT)	\$90.00
BX-08TD1	8	12–24 VDC, Sinking	\$63.00
BX-08TD2		12–24 VDC, Sourcing	\$67.00
BX-08TR		Relay Form A (SPST)	\$73.00
BX-08TA		120–240 VAC, Triac	\$117.00
BX-08TRZ		Relay Form A (SPST), no surge suppression	\$82.00
BX-12TD1	12	12–24 VDC, Sinking	\$98.00
BX-12TD2		12–24 VDC, Sourcing	\$90.00
BX-12TR		Relay Form A (SPST)	\$98.00
BX-12TA		120–240 VAC, Triac	\$137.00
BX-16TD1	16	12–24 VDC, Sinking	\$105.00
BX-16TD2		12–24 VDC, Sourcing	\$105.00
BX-16TF2		2–5 VDC, Sourcing/TTL	\$98.00
BX-16TD2W		12–24 VDC, Sourcing	\$189.00
BX-16TDY2		12–24 VDC, Sourcing	\$99.00
BX-16TN2		48 VDC, Sourcing	\$103.00
BX-16TR		Relay Form A (SPST)	\$111.00
BX-16TRZ		Relay Form A (SPST), no surge suppression	\$118.00
BX-32TD1	32	12–24 VDC, Sinking	\$150.00
BX-32TD2		12–24 VDC, Sourcing	\$149.00

BRX Discrete Expansion Modules

Discrete Combo Input / Output Modules

Seven (7) discrete input/output combo modules are available with DC sink/source inputs and sink/source/relay outputs. The Input/Output faceplate terminal bar is in blue and red, making it easy to distinguish between inputs and outputs and from other module types.



Discrete Combo Input / Output Modules					
Part Number	Points		Input Type	Output Type	Price
	Input	Output			
<u>BX-08CD3R</u>	4	4	12–24 VDC, Sinking/ Sourcing	12–48 VDC 24–240 VAC, Relay	\$73.00
<u>BX-12CD3D1</u>	8	4		12–24 VDC, Sinking	\$73.00
<u>BX-12CD3D2</u>				12–24 VDC, Sourcing	\$73.00
<u>BX-16CD3D1</u>	8	8		12–24 VDC, Sinking	\$90.00
<u>BX-16CD3D2</u>				12–24 VDC, Sourcing	\$97.00
<u>BX-16CF3F2</u>			2–5 VDC, Sinking/ Sourcing/TTL	2–5 VDC, Sourcing/TTL	\$82.00
<u>BX-8NN8TN2</u>			48 VDC, Sinking/ Sourcing	48 VDC, Sourcing	\$113.00

Expansion Module Support by Controller	
Controller Type	# Expansion Modules
BX-DM1E-M	8
BX-DM1-10	8
BX-DM1E-10	8
BX-DM1-18	8
BX-DM1E-18	8
BX-DM1-36	8
BX-DM1E-36	8
BX-DMIO*	8
BX-EBC100*	8
BX-MBIO*	8

* Remote I/O controllers do not support Motion Control and Communications Modules.

BRX Wiring Termination Options

Terminal Block Connectors

The terminal block connectors are provided in kits of multiple connectors that are ordered as a single part number. There are 2 different types of kits to choose from; one kit for the five (5), eight (8) and 12-point discrete, and one

kit for the analog modules and 16-point discrete modules. The five (5), eight (8) and 12-point discrete module kits each have (3) 5-pin 5mm connectors. The 8-point modules will use only 2 of the 5-pin connectors.

The five (5) and 12-point modules will use all three connectors. The analog and 16-point digital module kits include (2) 10-pin 3.81 mm connectors.

Terminal Block Connectors, 5, 8 and 12-Point Discrete Modules

Terminal Block Kits for 5-point, 8-point and 12-point Expansion Modules



BX-RTB08 (Kit - 3 pieces)



BX-RTB08-1 (Kit - 3 pieces)



BX-RTB08-2 (Kit - 3 pieces)

Terminal Block Specifications 5-, 8- & 12-Point Type


Part Number Single Block Set of 3 Blocks	<u>BX-RTB05</u> <u>BX-RTB08</u>	<u>BX-RTB05-1</u> <u>BX-RTB08-1</u>	<u>BX-RTB05-2</u> <u>BX-RTB08-2</u>
Price (Single Block)	\$9.00	\$7.50	\$8.50
Price (Kit)	\$16.00	\$15.00	\$16.00
Connector Type	Screw Type - 90-degree	Spring Clamp Type - 180-degree	Screw Type - 180-degree
Wire Exit	180-degree	180-degree	180-degree
Pitch	5.0 mm	5.0 mm	5.0 mm
Screw Size	M2.5	N/A	M2.5
Screw Torque Recommended	< 3.98 lb-in [0.45 N·m]	N/A	< 3.98 lb-in [0.45 N·m]
Screwdriver Blade Width	3.5 mm	3.5 mm	3.5 mm
Wire Gauge (Single Wire)	28-12 AWG	28-14 AWG	28-12 AWG
Wire Gauge (Dual Wire)	28-16 AWG	28-16 AWG (Dual Wire Ferrule Required)	28-16 AWG
Wire Strip Length	0.3 in [7.5 mm]	0.37 in [9.5 mm]	0.3 in [7.5 mm]
Equiv. Dinkle P/N	5ESDV-05P-BK	5ESDSR-05P-BK	5ESDF-05P-BK

Terminal Block Connectors, Analog Modules and 16-Point Discrete Modules

Terminal Block Kits for Analog and 16-point Discrete Expansion Modules



BX-RTB10 (Kit - 2 pieces)



BX-RTB10-1 (Kit - 2 pieces)



BX-RTB10-2 (Kit - 2 pieces)

Terminal Block Specifications 16-Point Type

Part Number	<u>BX-RTB10</u>	<u>BX-RTB10-1</u>	<u>BX-RTB10-2</u>
Price (Kit)	\$22.50	\$25.00	\$23.50
Connector Type	Screw Type 90-degree	Spring Clamp Type 180-degree	Screw Type 180-degree
Wire Exit	180-degree	180-degree	180-degree
Pitch	3.81 mm	3.81 mm	3.81 mm
Screw Size	M2	N/A	M2
Screw Torque Recommended	<1.77 lb-in [0.2 N·m]	N/A	<1.77 lb-in [0.2 N·m]
Screwdriver Blade Width	2.5 mm	2.5 mm	2.5 mm
Wire Gauge (Single Wire)	28-16 AWG	26-18 AWG	30-16 AWG
Wire Gauge (Dual Wire)	28-18 AWG	30-20 AWG (Dual Wire Ferrule Required)	30-18 AWG
Wire Strip Length	0.24 in [6mm]	0.35 in [9mm]	0.26 in [6.5 mm]
Equiv. Dinkle P/N	EC381V-10P-BK	ESC381V-10-BK	EC381F-10P-BK



NOTE: BX-RTB10 terminal blocks are included with Temperature Input modules.

BRX Wiring Termination Options

ZIPLink Wiring System

BRX expansion modules can be quickly connected to convenient **ZIPLink** remote terminal blocks for ease of wiring I/O devices. Your **ZIPLink** selection is dependent on the number of expansion module terminal points. The following tables list the connector options.



8-Point BRX Discrete Expansion Module ZIPLink Selector

Expansion Module Part No.	ZIPLink Module	ZIPLink Module Part No.	Qty Needed	ZIPLink Cable Part No.*	Qty Needed
BX-08ND3	Feedthrough	ZL-RTB20 (Standard) OR ZL-RTB20-1 (Compact)	1	ZL-BXEM-CBL10 ZL-BXEM-CBL10-1 ZL-BXEM-CBL10-2	1
BX-08NF3					
BX-08NA					
BX-08NB					
BX-08TD1					
BX-08TD2					
BX-08TR**					
BX-08TRZ**					
BX-08TA					
BX-08CD3R**					

* Select cable length: Blank = 0.5 m, -1 = 1.0m, -2 = 2.0m.

Available pigtail cables: [ZL-BXEM-CBL10-1P](#) = 1.0 m, [ZL-BXEM-CBL10-2P](#) = 2.0 m.

** The relay outputs are derated not to exceed 2A per common when used with the **ZIPLink** wiring system.

12 & 5-Point BRX Discrete Expansion Module ZIPLink Selector

Expansion Module Part No.	ZIPLink Module	ZIPLink Module Part No.	Qty Needed	ZIPLink Cable Part No.*	Qty Needed
BX-12ND3	Feedthrough	ZL-RTB20 (Standard) OR ZL-RTB20-1 (Compact)	1	ZL-BXEM-CBL15 ZL-BXEM-CBL15-1 ZL-BXEM-CBL15-2	1
BX-12NA					
BX-12NB					
BX-12TD1					
BX-12TD2					
BX-12TR**					
BX-05TRS					
BX-12TA					
BX-12CD3D1					
BX-12CD3D2					

* Select cable length: Blank = 0.5 m, -1 = 1.0m, -2 = 2.0m.

Available pigtail cables: [ZL-BXEM-CBL15-1P](#) = 1.0 m, [ZL-BXEM-CBL15-2P](#) = 2.0 m.

** The relay outputs are derated not to exceed 2A per common when used with the **ZIPLink** wiring system.

BRX Wiring Termination Options

16-Point BRX Discrete Expansion Module ZIPLink Selector					
Expansion Module Part No.	ZIPLink Module	ZIPLink Module Part No.	Qty Needed	ZIPLink Cable Part No. *	Qty Needed
BX-16ND3	Sensor	ZL-LTB16-24-1	1	ZL-BXEM-CBL20 ZL-BXEM-CBL20-1 ZL-BXEM-CBL20-2	1
BX-16NF3	Feedthrough	ZL-RTB20 (Standard) OR ZL-RTB20-1 (Compact)	1		
BX-16NA	Feedthrough				
BX-16NB	Feedthrough				
BX-16TD1	Feedthrough				
BX-16TD2	Relay (Sourcing)	ZL-RRL16-24-1 , ZL-RRL16W-24-1 , ZL-RRL16F-24-1	1		
	Relay (Sinking)	ZL-RRL16-24-2 , ZL-RRL16W-24-2 , ZL-RRL16F-24-2	1		
	Feedthrough	ZL-RTB20 (Standard) OR ZL-RTB20-1 (Compact)	1		
BX-16TF2					
BX-16TR**					
BX-16TRZ**					
BX-16CD3D1					
BX-16CD3D2					
BX-16CF3F2					
BX-16NN					
BX-16TD2W					
BX-16TDY2					
BX-16TN2					
BX-8NN8TN2					

* Select cable length: Blank = 0.5 m, -1 = 1.0m, -2 = 2.0m.

Available pigtail cables: [ZL-BXEM-CBL20-1P](#) = 1.0 m, [ZL-BXEM-CBL20-2P](#) = 2.0 m.

** The relay outputs are derated not to exceed 2A per common when used with the *ZIPLink* wiring system.

32-Point BRX Discrete Expansion Module ZIPLink Selector					
Expansion Module Part No.	ZIPLink Module	ZIPLink Module Part No.	Qty Needed	ZIPLink Cable Part No.*	Qty Needed
BX-32ND3	Sensor	ZL-LTB32-24-1	1	ZL-D24-CBL40 ZL-D24-CBL40-1 ZL-D24-CBL40-2	1
	Feedthrough	ZL-RTB40 (Standard) OR ZL-RTB40-1 (Compact)	1		
BX-32TD1	Feedthrough				
BX-32TD2					

* Select cable length: Blank = 0.5 m, -1 = 1.0m, -2 = 2.0m.

Available pigtail cables: [ZL-D24-CBL40-1P](#) = 1.0 m, [ZL-D24-CBL40-2P](#) = 2.0 m.

Suffix -X indicates 45° cable connector angle. Non -X indicates 180° cable connector angle.

16-Point BRX High Speed Expansion Module <i>ZIPLink</i> Selector					
Expansion Module Part No.	<i>ZIPLink</i> Module	<i>ZIPLink</i> Module Part No.	Qty Needed	<i>ZIPLink</i> Cable Part No. *	Qty Needed
BX-HSIO4	Feedthrough	ZL-RTB40 (Standard) OR ZL-RTB40-1 (Compact)	1	ZL-BX-CBL40-S ZL-BX-CBL40-1S	1

BRX Wiring Termination Options

BRX Analog and Temperature Expansion Module ZIPLink Selector					
Expansion Module Part No.	ZIPLink Module	ZIPLink Module Part No.	Qty Needed	ZIPLink Cable Part No. ¹	Qty Needed
BX-04ADM-1	Feedthrough	ZL-RTB20 (Standard) OR ZL-RTB20-1 (Compact)	1	ZL-BXEM-CBL20 ZL-BXEM-CBL20-1 ZL-BXEM-CBL20-2	1
BX-04AD-1					
BX-08AD-1					
BX-16AD-1					
BX-04AD-2B					
BX-08AD-2B					
BX-16AD-2B					
BX-04DA-1					
BX-08DA-1					
BX-04DA-2B					
BX-08DA-2B					
BX-2AD2DA-1					
BX-4AD2DA-1					
BX-2AD2DA-2B					
BX-4AD2DA-2B					
BX-08AD-3				ZL-BXEM-CBL10 ZL-BXEM-CBL10-1 ZL-BXEM-CBL10-2	1
BX-08DA-3					
BX-2AD2DA-3					
BX-4AD4DA-3					
BX-04THM	Temperature Input modules are not supported by the ZIPLink wiring system.				
BX-08THM					
BX-06RTD					
BX-08NTC					
BX-04UT					
BX-08UT					
BX-4THM4DA-1					
BX-4RTD4DA-1					
BX-4UT4DA-3					
BX-4UT4TD1					
BX-4UT4TD2					
BX-4UT4TR					

1. Select cable length: Blank = 0.5 m, -1 = 1.0m, -2 = 2.0m.

Available pigtail cables: [ZL-BXEM-CBL20-1P](#) = 1.0 m, [ZL-BXEM-CBL20-2P](#) = 2.0 m.