

BRX Pluggable Option Modules (POM)


BX-P-SER2-RJ12

\$76.00

The RS-232 RJ12 POM can be connected to the Do-more! Designer programming software, Modbus RTU master or slave devices, DirectLogic PLCs via K-Sequence

protocol, as well as devices that send or receive non-sequenced ASCII strings or characters.

Pin #	Signal
1	0V Power (-) connection (GND)
2	5V Power (+) connection (220mA max)
3	RXD Receive Data (RS-232)
4	TXD Transmit Data (RS-232)
5	RTS Request to Send (RS-232)
6	CTS Clear to Send (RS-232)



6-pin RJ12 Female Modular Connector



BX-P-SER2-RJ12 Specifications

Description	Non-isolated Serial port that can communicate via RS-232 Includes ESD protection and built-in surge protection.
Supported Protocols	Do-more!™ Protocol (Default) Modbus RTU (Master & Slave) K-Sequence (Slave) ASCII (In & Out)
Data Rates	1200, 2400, 4800, 9600, 19200, 38400, 57600, and 115200 Baud
Default Settings	115200bps, No Parity, 8 Data Bits, 1 Stop Bit, Station #1
Port Status LED	Green LED is illuminated when active for TXD and RXD
Port Type	RJ12 - 6P6C
RS-232 Maximum Output Load (TXD/RTS)	3kΩ, 1000pf
RS-232 Minimum Output Voltage Swing	±5V
RS-232 Output Short Circuit Protection	±15mA
Cable Requirements	RS-232 use P/N L19772-XXX from automationdirect.com
Maximum Distance	30 meters (100 feet); 6 meters (20 foot) recommended maximum
Replacement Connector	N/A
Hot Swappable	Yes