

0754SDSR41A-P Cut Sheet



Toshiba SD premium efficiency AC induction motor, high-performance inverter duty and severe duty, 75hp, 3-phase, 230/460 VAC, 1800rpm, TEFC, NEMA 365T frame, cast iron, rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/0754SDSR41A-P>

Technical Specifications

| | |
|--------------------------|--|
| Brand | Toshiba |
| Item | Motor |
| Series | SD |
| Efficiency Group | Premium efficiency |
| Efficiency | 95.4 |
| Voltage Type | AC |
| Motor Type | Induction |
| Motor Application | High-performance inverter duty and severe duty |
| Horsepower Rating | 75hp |
| Number of Phases | 3 |
| Voltage Rating | 230/460 VAC |
| Synchronous Speed | 1800rpm |
| Nameplate RPM | 1780rpm |
| Overload Type | None |
| Enclosure Type | TEFC |
| Shaft Type | Round with square key |

| | |
|---------------------------------|--------------------------------|
| Shaft Diameter | 2-3/8in |
| Shaft Material | 1045 hot rolled (C-204) steel |
| Motor Frame | NEMA 365T |
| Frame Material | Cast iron |
| Electrically Reversible | Yes |
| Insulation Class | Class F |
| IP Rating | IP55 |
| Constant Torque Rating | 20:1 |
| Variable Torque Rating | 60:1 |
| Service Factor | 1.15 |
| Integrated Brake | No |
| NEMA Design | Design B |
| Junction Box Orientation | F1 |
| Mounting | Rigid base |
| Mounting Orientation | Horizontal or shaft down |
| Additional Information | Class I Div 2 hazardous rating |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E133052 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | 2637147 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/0754SDSR41A-P.pdf>
See store item page for other formats.