

# 10.02.01.01606 Cut Sheet

Schmalz basic vacuum ejector, 860.0 l/min (30.4 cfm) suction rate, 3/8in female NPT inlet(s), 1in female NPT vacuum port.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/10.02.01.01606>

## Technical Specifications

<b>Brand</b>	Schmalz
<b>Item</b>	Vacuum ejector
<b>Ejector Type</b>	Basic
<b>Degree of Evacuation</b>	60%
<b>Suction Rate</b>	860.0 l/min (30.4 cfm)
<b>Air Consumption</b>	300.0 l/min (10.6 cfm)
<b>Average Noise Level</b>	69 dbA
<b>Inlet Port</b>	3/8in female NPT
<b>Vacuum Port</b>	1in female NPT
<b>Air Saving</b>	No
<b>Includes</b>	Mounting hardware
<b>Alternate ID</b>	SBPL-100-HF-NPT

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/10.02.01.01606.pdf>  
See store item page for other formats.