

1120250300XP Cut Sheet



Metal Work pneumatic cylinder, ISO 6432 non-repairable, 25mm bore, 10mm rod diameter, 300mm stroke, double acting, magnetic piston, universal mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1120250300XP>

Technical Specifications

Brand	Metal Work
Item	Cylinder
Working Fluid	Air or inert gas
Cylinder Type	ISO 6432 non-repairable
Bore Diameter	25mm
Stroke	300mm
Port Size	G1/8 female BSPP
Mounting	Universal

Action Type	Double acting
Magnetic Piston	Magnetic piston
Body Material	Stainless steel
End Cap Material	Aluminum
Rod Material	Stainless steel
Rod Diameter	10mm
Rod Thread Size	M10x1.25
Bushing Type	Bronze bushings

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/1120250300XP.pdf>
See store item page for other formats.