

1151E-6504 Cut Sheet



Eaton photoelectric sensor, rectangular, plastic housing, through-beam emitter, infrared light emission, 500ft sensing distance, 12-240 VDC/24-240 VAC operating voltage, 4-wire, 4-pin mini connector and 7/8in - 16UNF thread.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1151E-6504>

Technical Specifications

Brand	Eaton
Item	Photoelectric sensor
Shape	Rectangular
Housing Size	73 x 48.5 x 46mm
Thread mounting base size	30mm
IP Rating	IP67
Housing Material	Plastic
Sensing Method	Through-beam emitter

Operating Voltage	12-240 VDC/24-240 VAC
Number of Wires	4
Sensing Distance	500ft
Sensitivity	Potentiometer
Light Emission	Infrared
Connection	4-pin mini connector and 7/8in - 16UNF thread
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document