

# 12351010005 Cut Sheet



Pfannenberg air-to-water heat exchanger, 3241 BTU/H, 115 VAC operating voltage, 60 Hz, 0.69A running current, side mount, galvanized steel, RAL 7035 light gray, powder coat finish. For use with NEMA/UL Type 3R & 4 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/12351010005>

## Technical Specifications

Brand	Pfannenberg
Item	Air-to-water Heat exchanger
Cooling Capacity	3241 BTU/H
Operating Voltage	115 VAC
Frequency	60 Hz
Running Current	0.69A
Mounting	Side
Housing Material	Galvanized steel
Color	RAL 7035 light gray
Finish	Powder coat
For Use With	NEMA/UL Type 3R & 4 enclosures
Includes	Mounting template and hardware

## Agency Approvals

UL Listed File #	SA10300
UL Recognized File #	SA10300
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/12351010005.pdf>  
See store item page for other formats.