

1351E-6534 Cut Sheet



Eaton photoelectric sensor, rectangular, diffuse, infrared, 10ft sensing distance, selectable light-on/dark-on, SPDT EM relay, potentiometer, 66 Hz switching frequency, plastic housing, 5-pin AC micro connector and 1/2in - 20UNF thread.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1351E-6534>

Technical Specifications

Brand	Eaton
Item	Photoelectric sensor
Shape	Rectangular
Housing Size	72 x 48.5 x 46mm
Thread mounting base size	30mm
IP Rating	IP67
Housing Material	Plastic
Sensing Method	Diffuse
Operating Voltage	12-240 VDC/24-240 VAC
Number of Wires	5

Switching Output	SPDT EM relay
Sensing Distance	10ft
Sensitivity	Potentiometer
Operation Mode	Selectable light-on/dark-on
Switching Frequency	66 Hz
Light Emission (NP)	Infrared
Cable Length	7.5in/190.5mm
Connection	5-pin AC micro connector and 1/2in - 20UNF thread
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document