

# 14990863 Cut Sheet



WEG Electric CFW500 series AC high-performance drive with disconnect, NEMA 4X, 230 VAC, 1/4hp with 3-phase and 1-phase input, SVC, V/Hz, VVW, FOC or torque mode, A frame, RS-485, Modbus RTU, 65kA SCCR. Optional communication and STO modules available.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/14990863>

## Technical Specifications

<b>Brand</b>	WEG Electric
<b>Item</b>	Drive with disconnect
<b>Controller Type</b>	High-performance
<b>Series</b>	CFW500
<b>Voltage Type</b>	AC
<b>Nominal Drive Input Voltage</b>	230 VAC
<b>Nominal Drive Output Voltage</b>	230 VAC
<b>Number of Input Phases</b>	3 and 1
<b>Number of Output Phases</b>	3
<b>Horsepower By Input Phase</b>	1/4hp with 3-phase and 1-phase input
<b>Amperage Rating</b>	1.6A
<b>Control Mode</b>	SVC, V/Hz, VVW, FOC or torque
<b>Safe Torque Off (STO)</b>	No
<b>Temperature Rating</b>	0 to 50 deg C
<b>Enclosure Type</b>	NEMA 4X
<b>IP Rating</b>	IP66
<b>Mounting</b>	Wall
<b>Frame Size</b>	A
<b>Dynamic Braking</b>	Integrated dynamic braking unit
<b>Communication Port and Connection Type(s)</b>	(1) RS-485 (3-pin terminal)
<b>Port Protocol(s)</b>	Modbus RTU Master/Slave
<b>Port Speed(s)</b>	up to 38.4k baud
<b>Input Signal</b>	4-20 mA, voltage or potentiometer input
<b>Output Type</b>	PWM output
<b>Reverse Capability</b>	Built-in
<b>Internally Bypassed</b>	No
<b>Carrier Frequency Range</b>	2.5-15 kHz
<b>Output Frequency Range</b>	0.1-500 Hz

<b>Number of Analog Input Channels</b>	1
<b>Number Of Input Channels</b>	1
<b>Analog Input Signal Type</b>	Current/voltage
<b>Number of Non-Isolated Analog Input Commons</b>	1
<b>Number of Points per Analog Input Common</b>	1
<b>Input Resolution</b>	10-bit
<b>Input Current Signal Range</b>	0-20 mA, 4-20 mA
<b>Input Voltage Signal Range</b>	0-10 VDC
<b>Number of Analog Output Channels</b>	1
<b>Number Of Output Channels</b>	1
<b>Analog Output Signal Type</b>	Current/voltage
<b>Number of Non-Isolated Analog Output Commons</b>	1
<b>Number of Points per Analog Output Common</b>	1
<b>Output Resolution</b>	10-bit
<b>Output Current Signal Range</b>	0-20 mA and 4-20 mA
<b>Output Voltage Signal Range</b>	0-10 VDC
<b>Number of Discrete Input Points</b>	4
<b>Nominal Discrete Input Voltage</b>	24 VDC
<b>Discrete Input Type</b>	Sourcing/sinking
<b>Number of Non-Isolated Discrete Input Commons</b>	1
<b>Number of Points per Discrete Input Common</b>	1
<b>Number of Discrete Output Points</b>	2

# 14990863 Cut Sheet

<b>Nominal Discrete Output Voltage</b>	240 VAC and 24 VDC
<b>Discrete Output Type</b>	Relay
<b>Relay Configuration</b>	(1) Form C (SPDT) relay
<b>Number of Non-Isolated Discrete Output Commons</b>	1
<b>Number of Points per Discrete Output Common</b>	1
<b>Load Current</b>	0.5A/point relay, 150 mA/point discrete
<b>Fuse Type</b>	User-supplied external fuse
<b>Programming Language</b>	Ladder
<b>SCCR Rating</b>	65kA SCCR
<b>Connector Type</b>	Screw terminal
<b>For Use With</b>	3-phase induction and permanent magnet AC motors
<b>Additional Information</b>	Optional communication and STO modules available
<b>Manufacturer Part Number</b>	CFW500A01P6B2DB66DSG2

## Agency Approvals

<b>UL Listed File #</b>	E184430
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>