

# CF Series Fiberglass In-Line Pushbutton Enclosures 30mm and 22mm with Lift-off Cover

**STÄHLIN**  
A ROBROY ENCLOSURES® BRAND



## Construction

- Hot compression molded fiberglass reinforced thermoset polyester
- Poured polyurethane seamless gasket provides watertight, dust-tight environmental seal
- Recessed captive stainless steel screws
- 300 Series stainless steel used on all external hardware
- Workable material cuts, drills, punches and saws with ease and accuracy
- Optional mounting feet
- Rounded edges, minimal protrusions or exposed pocket prevents accumulation of dust or debris
- 
- Metal grounding strap
- Submersible, non-corrosive environmental design
- Lift-off cover with four cover screws
- Non-conductive, impact-resistant, UV-resistant
- Non-flame propagating
- Subpanel not required
- Smooth surface, no color variations, swirls or color pockets, no voids
- Color: Gray

## Listings

- UL/cUL [File E64358]
- NEMA Types 1, 3R, 4X, 6P, and 12 [Files 508A, 50, and 50e]
- CSA Standard C22.2 Types 1, 3R, 4X, 6P, and 12 [File LR069014]
- IEC 60529 Ratings IP66, IP67, IP68 [File E362920]
- UL 1741 [File E333478]
- Temperature Range -76°F to +274°F [-60°C to +134°C]
- Flammability Rating UL94-5V
  - Self-extinguishing
  - Non-halogenated
  - Non-flame propagating
- NFPA No. 101 Flame Spread Class A (1)

## Certifications

- cULus, CSA, IEC, REACH
- Outdoor UV Exposure Rated [UL 746C (F1)]
- Plenum Space Rating [File 2043]



CF Series 30mm Fiberglass In-Line Pushbutton				
Part Number	Price	# Holes	Enclosure Overall Size HxWxD	Drawing Link
<a href="#">CF6PB</a>	\$66.00	1	6.63 x 3.81 x 3.89 [168 x 97 x 99]	<a href="#">PDF</a>
<a href="#">CF2PB</a>	\$68.00	2	6.63 x 3.81 x 3.89 [168 x 97 x 99]	<a href="#">PDF</a>
<a href="#">CF3PB</a>	\$74.00	3	8.88 x 3.81 x 3.89 [226 x 97 x 99]	<a href="#">PDF</a>
<a href="#">CF4PB</a>	\$75.00	4	11.13 x 3.81 x 3.89 [283 x 97 x 99]	<a href="#">PDF</a>
<a href="#">CF5PB</a>	\$87.00	5	13.78 x 3.63 x 3.14 [350 x 92 x 80]	<a href="#">PDF</a>
<a href="#">CF6PB</a>	\$101.00	6	17.35 x 3.63 x 3.14 [441 x 92 x 80]	<a href="#">PDF</a>

Notes: Subpanels not required.  
Dimensions in inches [millimeters].



CF Series 22mm Fiberglass In-Line Pushbutton				
Part Number	Price	# Holes	Enclosure Overall Size HxWxD	Drawing Link
<a href="#">CF1PB22</a>	\$66.00	1	6.63 x 3.81 x 3.89 [168 x 97 x 99]	<a href="#">PDF</a>
<a href="#">CF2PB22</a>	\$68.00	2	6.63 x 3.81 x 3.89 [168 x 97 x 99]	<a href="#">PDF</a>
<a href="#">CF3PB22</a>	\$74.00	3	6.63 x 3.81 x 3.89 [168 x 97 x 99]	<a href="#">PDF</a>
<a href="#">CF4PB22</a>	\$75.00	4	8.88 x 3.81 x 3.89 [226 x 97 x 99]	<a href="#">PDF</a>
<a href="#">CF5PB22</a>	\$87.00	5	11.13 x 3.81 x 3.89 [283 x 97 x 99]	<a href="#">PDF</a>
<a href="#">CF6PB22</a>	\$101.00	6	11.13 x 3.81 x 3.89 [283 x 97 x 99]	<a href="#">PDF</a>

Notes: Subpanels not required.  
Dimensions in inches [millimeters].

