

151074 Cut Sheet



FATH swivel foot threaded rod, silver, 1/4-20 UNC x 1-1/2in, zinc plated steel, ball joint size 15. For use with all rails. Requires ball joint size 15 swivel base and 1/4-20 UNC thread transport/base plate. Manufacturer part number: 098DU1/4-1,5M.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/151074>

Technical Specifications

Brand	FATH
Item	Swivel foot threaded rod
Series	10 Series, 15 Series, 30 Series, 40 Series and 45 Series
Color	Silver
Thread Size	1/4-20 UNC x 1-1/2in
Material	Zinc plated steel

Load Rating	463 lb/210 kg
Ball Joint Size	15
For Use With	All rails
Requires	Ball joint size 15 swivel base and 1/4-20 UNC thread transport/base plate
Manufacturer Part Number	098DU1/4-1,5M

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/151074.pdf>
See store item page for other formats.