

# 15734119 Cut Sheet



WEG Electric CFW500 series AC high-performance drive, enclosed, 460 VAC, 60hp with 3-phase input, SVC, V/Hz, VVW, FOC, encoder or torque mode, F frame, RS-485, integrated dynamic braking. Optional communication and STO modules available.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/15734119>

## Technical Specifications

<b>Brand</b>	WEG Electric
<b>Item</b>	Drive
<b>Controller Type</b>	High-performance
<b>Series</b>	CFW500
<b>Voltage Type</b>	AC
<b>Nominal Drive Input Voltage</b>	460 VAC
<b>Nominal Drive Output Voltage</b>	460 VAC
<b>Number of Input Phases</b>	3
<b>Number of Output Phases</b>	3
<b>Horsepower By Input Phase</b>	60hp with 3-phase input
<b>Amperage Rating</b>	88A
<b>Variable Torque Amperage Rating</b>	105A
<b>Control Mode</b>	SVC, V/Hz, VVW, FOC, encoder or torque
<b>Safe Torque Off (STO)</b>	No
<b>Temperature Rating</b>	-10 to 40 deg C
<b>Enclosure Type</b>	Enclosed
<b>IP Rating</b>	IP20
<b>Mounting</b>	Panel, wall or flange
<b>Frame Size</b>	F
<b>Dynamic Braking</b>	Integrated dynamic braking
<b>Communication Port and Connection Type(s)</b>	(1) RS-485 (3-pin terminal)
<b>Port Protocol(s)</b>	Modbus RTU Master/Slave
<b>Port Speed(s)</b>	up to 38.4k baud
<b>Input Signal</b>	4-20 mA, voltage or potentiometer input
<b>Output Type</b>	PWM output
<b>Reverse Capability</b>	Built-in
<b>Internally Bypassed</b>	No
<b>Carrier Frequency Range</b>	2.5-15 kHz
<b>Output Frequency Range</b>	0.1-500 Hz
<b>Number of Analog Input Channels</b>	1
<b>Number Of Input Channels</b>	1

<b>Analog Input Signal Type</b>	Current/voltage
<b>Number of Non-Isolated Analog Input Commons</b>	1
<b>Number of Points per Analog Input Common</b>	1
<b>Input Resolution</b>	10-bit
<b>Input Current Signal Range</b>	0-20 mA and 4-20 mA
<b>Input Voltage Signal Range</b>	0-10 VDC
<b>Number of Analog Output Channels</b>	1
<b>Number Of Output Channels</b>	1
<b>Analog Output Signal Type</b>	Current/voltage
<b>Number of Non-Isolated Analog Output Commons</b>	1
<b>Number of Points per Analog Output Common</b>	1
<b>Output Resolution</b>	10-bit
<b>Output Current Signal Range</b>	0-20 mA and 4-20 mA
<b>Output Voltage Signal Range</b>	0-10 VDC
<b>Number of Discrete Input Points</b>	4
<b>Nominal Discrete Input Voltage</b>	24 VDC
<b>Discrete Input Type</b>	Sourcing/sinking
<b>Number of Non-Isolated Discrete Input Commons</b>	1
<b>Number of Points per Discrete Input Common</b>	1
<b>Number of Discrete Output Points</b>	2
<b>Nominal Discrete Output Voltage</b>	240 VAC and 24 VDC
<b>Discrete Output Type</b>	Sinking/relay
<b>Relay Configuration</b>	(1) Form C (SPDT) relay
<b>Number of Non-Isolated Discrete Output Commons</b>	1

# 15734119 Cut Sheet

Number of Points per Discrete Output Common	1
Load Current	0.5A/point relay, 150 mA/point discrete
Fuse Type	User-supplied external fuse
Programming Language	Ladder
Connector Type	Screw terminal
For Use With	3-phase induction and permanent magnet AC motors
Additional Information	Optional communication and STO modules available
Manufacturer Part Number	CFW500F0105T4DB20G2

## Agency Approvals

UL Listed File #	E184430
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/15734119.pdf>  
See store item page for other formats.