

# 16905714 Cut Sheet



WEG Electric CFW500 series AC high-performance drive with disconnect, NEMA 4X, 230 VAC, 15hp with 3-phase input, SVC, V/Hz, VVW, FOC, encoder or torque mode, C frame, RS-485, integrated dynamic braking. Optional communication and STO modules available.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/16905714>

## Technical Specifications

Brand	WEG Electric
Item	Drive with disconnect
Controller Type	High-performance
Series	CFW500
Voltage Type	AC
Nominal Drive Input Voltage	230 VAC
Nominal Drive Output Voltage	230 VAC
Number of Input Phases	3
Number of Output Phases	3
Horsepower By Input Phase	15hp with 3-phase input
Amperage Rating	47A
Control Mode	SVC, V/Hz, VVW, FOC, encoder or torque
Safe Torque Off (STO)	No
Temperature Rating	-10 to 40 deg C
Enclosure Type	NEMA 4X
IP Rating	IP66
Mounting	Wall
Frame Size	C
Dynamic Braking	Integrated dynamic braking
Communication Port and Connection Type(s)	(1) RS-485 (3-pin terminal)
Port Protocol(s)	Modbus RTU Master/Slave
Port Speed(s)	up to 38.4k baud
Input Signal	4-20 mA, voltage or potentiometer input
Output Type	PWM output
Reverse Capability	Built-in
Internally Bypassed	No
Carrier Frequency Range	2.5-15 kHz
Output Frequency Range	0.1-500 Hz
Number of Analog Input Channels	1
Number Of Input Channels	1
Analog Input Signal Type	Current/voltage

Number of Non-Isolated Analog Input Commons	1
Number of Points per Analog Input Common	1
Input Resolution	10-bit
Input Current Signal Range	0-20 mA and 4-20 mA
Input Voltage Signal Range	0-10 VDC
Number of Analog Output Channels	1
Number Of Output Channels	1
Analog Output Signal Type	Current/voltage
Number of Non-Isolated Analog Output Commons	1
Number of Points per Analog Output Common	1
Output Resolution	10-bit
Output Current Signal Range	0-20 mA and 4-20 mA
Output Voltage Signal Range	0-10 VDC
Number of Discrete Input Points	4
Nominal Discrete Input Voltage	24 VDC
Discrete Input Type	Sourcing/sinking
Number of Non-Isolated Discrete Input Commons	1
Number of Points per Discrete Input Common	1
Number of Discrete Output Points	2
Nominal Discrete Output Voltage	240 VAC and 24 VDC
Discrete Output Type	Sinking/relay
Relay Configuration	(1) Form C (SPDT) relay
Number of Non-Isolated Discrete Output Commons	1

# 16905714 Cut Sheet

Number of Points per Discrete Output Common	1
Load Current	0.5A/point relay, 150 mA/point discrete
Fuse Type	User-supplied external fuse
Programming Language	Ladder
Connector Type	Screw terminal
For Use With	3-phase induction and permanent magnet AC motors
Additional Information	Optional communication and STO modules available
Manufacturer Part Number	CFW500C47P0T2DB66DSG2

## Agency Approvals

EU REACH	<a href="#">View EU REACH document</a>
----------	--

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/16905714.pdf>  
See store item page for other formats.