23152635000 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



Pfannenberg PROTECT PRO X 10 series Xenon tube audible-visual signal beacon, 116 dB at 1m, (80) selectable tone(s), flashing strobe (1 Hz flash frequency), red, 214 x 167 x 148mm, 11–60 VDC, IP66 and IP67, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/23152635000

Technical Specifications

Brand	Pfannenberg
Item	Audible-visual signal beacon
Series	PROTECT PRO X 10
Bulb Type	Xenon tube
Operator Size	214 x 167 x 148mm
Operator Color	Red
Light Color(s)	Red
Light Function	Flashing strobe (1 Hz flash frequency)
Housing Material	Aluminium/ABS plastic
Material	Aluminium/ABS plastic

Loudness Decibel	116 dB at 1m
Tone Frequency	150 Hz to 2.9 kHz
Tone Type	(80) selectable
Touch to Acknowledge	No
Number of Alarms	80
Voltage Rating	11–60 VDC
Mounting	Surface
IP Rating	IP66 and IP67
NEMA Rating	4/4X
Connection	Screw terminal

Agency Approvals

UL Listed File #	S7256
UL Recognized File #	NONE
UL Hazardous File #	NONE
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes with Exemptions (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/23152635000.pdf
See store item page for other formats.