

246516UNC3 Cut Sheet



RUKO hand tap, 5/16-18 UNC, square shank per DIN 10, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/246516UNC3>

Technical Specifications

| | |
|----------------|---|
| Brand | RUKO |
| Item | Hand tap |
| Thread | 5/16-18 UNC per ANSI/ASME B1.1 |
| Thread Length | 0.87in |
| Overall Length | 2.2in (56mm) |
| Tap Drill Size | Letter size F |
| Shank | Square shank per DIN 10 |
| Material | High-speed steel (HSS) |
| Finish | Bright |
| For Use On | Aluminum, brass, plastic, steel, bronze and cast iron |
| Application | Thread making |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |