

CT Series NEMA 3R Double-Door Hinge Cover



CT Series NEMA 3R Double-Door Hinge Cover			
Part Number	Price	Body/Door Steel Gauge	Enclosure Size HxWxD
CTDD302410	\$398.00	14/14	24x30x10 [610x762x254]
CTDD303012	\$447.00	12/12	30x30x12 [762x762x305]
CTDD303612	\$498.00		36x30x12 [914x762x305]
CTDD362412	\$425.00	14/14	24x36x12 [610x914x305]
CTDD363012	\$482.00	12/12	30x36x12 [762x914x305]
CTDD363212	\$495.00		32x36x12 [813x914x305]
CTDD363612	\$582.00		36x36x12 [914x914x305]
CTDD363616	\$604.00		36x36x16 [914x914x406]
CTDD424212	\$636.00		42x42x12 [1118x1118x305]
CTDD443012	\$473.00		30x44x12 [762x1067x305]
CTDD484816	\$750.00		48x48x16 [1219x1219x406]

Note: Dimensions in inches [millimeters]; letters in table correspond to letters on dimensional drawings.

Applications

Designed as a housing for current and voltage transformers, recorders, meters, relays and/or for terminal instrumentation. Can also be used as a service or junction box.

Construction

- Manufactured from 14 and 12 gauge carbon steel
- Fully seam welded and ground smooth, with weep hole
- Drip shield
- Lift-off hinges, gasketed doors
- Supplied with non-locking "T" handle
- Meter seal provisions
- Mounting holes in back provided
- Supplied with studs in back of enclosure to support optional wood subpanel [available from Hubbell Wiegmann]

Finish

- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces

Listings


- UL Listed Type 3R [UL file E23553]
- CSA file LL66078



Enclosure Shipping Schedule
1 -10 days

Color indicates shipping lead time in business days.

Dimensions in [mm]



See our website: www.AutomationDirect.com for complete engineering drawings.