

# .3336ES3E56C-S Cut Sheet



WEG Electric S standard efficiency AC induction motor, general purpose and inverter rated, 1/3hp, 3-phase, 208-230/460 VAC, 3600rpm, TEFC, NEMA 56C frame, rolled steel, C-face/rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/.3336ES3E56C-S>

## Technical Specifications

|                          |                                    |
|--------------------------|------------------------------------|
| <b>Brand</b>             | WEG Electric                       |
| <b>Item</b>              | Motor                              |
| <b>Series</b>            | S                                  |
| <b>Efficiency Group</b>  | Standard efficiency                |
| <b>Efficiency</b>        | 62                                 |
| <b>Voltage Type</b>      | AC                                 |
| <b>Motor Type</b>        | Induction                          |
| <b>Motor Application</b> | General purpose and inverter rated |
| <b>Horsepower Rating</b> | 1/3hp                              |
| <b>Number of Phases</b>  | 3                                  |
| <b>Voltage Rating</b>    | 208-230/460 VAC                    |
| <b>Synchronous Speed</b> | 3600rpm                            |
| <b>Nameplate RPM</b>     | 3485rpm                            |
| <b>Overload Type</b>     | None                               |
| <b>Enclosure Type</b>    | TEFC                               |
| <b>Shaft Type</b>        | Round with square key              |

|                                 |                                |
|---------------------------------|--------------------------------|
| <b>Shaft Diameter</b>           | 5/8in                          |
| <b>Shaft Material</b>           | 1045 carbon steel              |
| <b>Motor Frame</b>              | NEMA 56C                       |
| <b>Frame Material</b>           | Rolled steel                   |
| <b>Electrically Reversible</b>  | Yes                            |
| <b>Insulation Class</b>         | Class F                        |
| <b>IP Rating</b>                | IP55                           |
| <b>Constant Torque Rating</b>   | 10:1                           |
| <b>Variable Torque Rating</b>   | 1000:1                         |
| <b>Service Factor</b>           | 1.15                           |
| <b>Integrated Brake</b>         | No                             |
| <b>Junction Box Orientation</b> | F1                             |
| <b>Mounting</b>                 | C-face/rigid base              |
| <b>Mounting Orientation</b>     | Horizontal or vertical         |
| <b>Additional Information</b>   | Class I Div 2 hazardous rating |

## Agency Approvals

|                         |  |
|-------------------------|--|
| <b>UL Listed File #</b> | E104590                                |
| <b>CE</b>               | None                                   |
| <b>CSA File #</b>       | LR38324                                |
| <b>RoHS Status</b>      | No                                     |
| <b>EU REACH</b>         | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/.3336ES3E56C-S.pdf>  
See store item page for other formats.