

57105267 Cut Sheet



WERMA audible signal horn with trumpet, 108 dB at 1m, 100 Hz tone frequency, continuous tone(s), 115 VAC, wall mount, aluminum housing, dark gray, IP55.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/57105267>

Technical Specifications

Brand	WERMA
Item	Audible signal horn with trumpet
Loudness Decibel	108 dB at 1m
Tone Frequency	100 Hz
Tone Type	Continuous
Touch to Acknowledge	No
Number of Alarms	1
Voltage Rating	115 VAC
Mounting	Wall
Housing Material	Aluminum
Color	Dark gray
IP Rating	IP55

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/57105267.pdf>
See store item page for other formats.