

011630-02 Cut Sheet



Stego thermostat, dual fixed, N.C. (open on rise) 41 deg F (5 deg C) switch-on, N.O. (close on rise) 95 deg F (35 deg C) switch-on, 18 deg F (10K) switching differential, 35mm DIN rail mount, for electrical enclosure climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/011630-02>

Technical Specifications

Brand	Stego
Item	Thermostat
IP Rating	IP20
Setpoint Type	Dual fixed
Contact 1	N.C. (open on rise) 41 deg F (5 deg C) switch-on
Contact 2	N.O. (close on rise) 95 deg F (35 deg C) switch-on
Switching Differential	18 deg F (10K)
Switching Tolerance	Varies, see specifications
Maximum Switching Capacity	10A resistive / 2A inductive at 120 VAC, 5A resistive / 1.6A inductive at 240 VAC, 30W DC
Connection	4-pole terminal for 14 AWG max solid or 16 AWG max stranded wire
Mounting	35mm DIN rail
Application	For electrical enclosure climate control

Agency Approvals

UL Listed File #	None
UL Recognized File #	E164102
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/011630-02.pdf>
See store item page for other formats.