



Stego thermostat, dual adjustable, N.C. (open on rise) 0 to 60 deg C, N.O. (close on rise) 0 to 60 deg C, 7K switching differential, 35mm DIN rail mount, for electrical climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/011720-00>

Technical Specifications

| | |
|-----------------------------------|--|
| Brand | Stego |
| Item | Thermostat |
| IP Rating | IP20 |
| Setpoint Type | Dual adjustable |
| Contact 1 | N.C. (open on rise) 0 to 60 deg C |
| Contact 2 | N.O. (close on rise) 0 to 60 deg C |
| Switching Differential | 7K |
| Switching Tolerance | +/-4K |
| Maximum Switching Capacity | 15A resistive / 2A inductive at 120 VAC, N.C. |
| Connection | 4-pole terminal for 14 AWG max solid or 16 AWG max stranded wire |
| Mounting | 35mm DIN rail |
| Application | For electrical enclosure climate control |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E164102 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 215952 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |
| Other | None |