

# 011750-01 Cut Sheet



Stego thermostat, dual adjustable, N.C. (open on rise) 14 to 122 deg F, N.O. (close on rise) 68 to 176 deg F, 12.6 deg F switching differential, 35mm DIN rail mount, for electrical enclosure climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/011750-01>

## Technical Specifications

Brand	Stego
Item	Thermostat
IP Rating	IP20
Setpoint Type	Dual adjustable
Contact 1	N.C. (open on rise) 14 to 122 deg F
Contact 2	N.O. (close on rise) 68 to 176 deg F
Switching Differential	12.6 deg F
Switching Tolerance	+/-7 deg F

Maximum Switching Capacity	15A resistive / 2A inductive at 120 VAC, N.C.: 10A resistive / 2A inductive at 250 VAC, N.O.: 5A resistive / 2A inductive at 250 VAC, 30W DC
Connection	4-pole terminal for 14 AWG max solid or 16 AWG max stranded wire
Mounting	35mm DIN rail
Application	For electrical enclosure climate control

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E164102
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	215952
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/011750-01.pdf>  
See store item page for other formats.