

# 58501 Cut Sheet



Viking jobber-length drill bit and machine tap set, 12 pieces, high-speed steel (HSS), round and square shank, UNC thread type, imperial, number and letter, gold oxide finish, metal index case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/58501>

## Technical Specifications

<b>Brand</b>	Viking
<b>Item</b>	Drill bit and machine tap set
<b>Number of Pieces</b>	12
<b>Material</b>	High-speed steel (HSS)
<b>Drill Bit Type</b>	Jobber-length
<b>Thread Type</b>	UNC
<b>Thread</b>	#6-32 UNC, #8-32 UNC, #10-24 UNC, #10-32 UNF, 1/4-20 UNC and 5/16-18 UNC
<b>Drill Bit Size</b>	Wire number size 36, wire number size 29, wire number size 25, wire number size 21, wire number size 7 and letter size F
<b>Finish</b>	Gold oxide
<b>Point Angle</b>	135 degrees

<b>Point Cut</b>	Split
<b>Shank Type</b>	Round and square
<b>Application</b>	Thread making and hole cutting
<b>For Use On</b>	Stainless steel, iron and steel
<b>Measurement Type</b>	Imperial, number and letter
<b>Package Type</b>	Metal index case
<b>Set Includes</b>	Includes (6) jobber-length drill bits (wire number size 36, wire number size 29, wire number size 25, wire number size 21, wire number size 7, letter size F), (6) machine taps (#6-32 UNC, #8-32 UNC, #10-24 UNC, #10-32 UNF, 1/4-20 UNC, 5/16-18 UNC), durable metal case

## Agency Approvals

<b>UL Listed File #</b>	N/A
<b>UL Recognized File #</b>	N/A
<b>UL Hazardous File #</b>	N/A
<b>CE</b>	None
<b>CSA File #</b>	N/A
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>