

012469-00 Cut Sheet



Stego electronic hygrosat, fixed, 65% relative humidity, 5% RH switching differential, 120 VAC operating voltage, 35mm DIN rail mount, for electrical enclosure climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/012469-00>

Technical Specifications

Brand	Stego
Item	Electronic hygrosat
IP Rating	IP20
Setpoint Type	Fixed
Contact 1	65% relative humidity
Switching Differential	5% RH
Switching Tolerance	+/-1% at 77 deg F and 50% RH
Reaction Time	5 seconds

Operating Voltage	120 VAC
Maximum Switching Capacity	8A resistive / 1.6A inductive
Connection	5-pole terminal for 14 AWG max solid or stranded wire
Indicating Type	LED indication
Mounting	35mm DIN rail
Application	For electrical enclosure climate control

Agency Approvals

UL Listed File #	None
UL Recognized File #	E164102
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/012469-00.pdf>
See store item page for other formats.