



Murrelektronik IO-Link hub, up to (4) temperature input channel(s), (4) 5-pin M12 A-coded port(s), RTD, 24-bit, IO-Link v1.1.2 (compatible with v1.1.3), IO-Link Class A Device, IP65, IP67 and IP68. Requires IO-Link master.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/59841>

Technical Specifications

Brand	Murrelektronik
Item	IO-Link hub
Number of Temperature Input Channels (TXT)	Up to (4)
Analog I/O Port Type(s)	(4) 5-pin M12 A-coded
Analog Input Signal Type	RTD
Input RTD Signal Types	Pt100, Pt100 climate, Pt200, Pt500, Pt1000, Ni100, Ni120, Ni200, Ni500 and Ni1000
Input Resistance Signal Range	0-3000 ohm
Input Resolution	24-bit
IO-Link Version	IO-Link v1.1.2 (compatible with v1.1.3)

Communication Port and Connection Type(s)	(1) 5-pin M12 A-coded (IO-Link)
Port Protocol(s)	IO-Link Class A Device
Port Speed(s)	IO-Link COM3
Indicator	LED
IP Rating	IP65, IP67 and IP68
Temperature Rating	-25 to 70 deg C
Includes	Marking tags
Requires	IO-Link master
Programming Software	Murrelektronik IO-Link Device Tool v4.0 or later

Agency Approvals

UL Listed File #	E201820
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/59841.pdf>
See store item page for other formats.