

# 60104 Cut Sheet



Viking machine tap, M4 X 0.70 UNC, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/60104>

## Technical Specifications

<b>Brand</b>	Viking	<b>Overall Length</b>	2.5in (64mm)
<b>Item</b>	Machine tap	<b>Tap Drill Size</b>	3.3mm
<b>Thread</b>	M4 X 0.70 UNC	<b>Material</b>	High-speed steel (HSS)
<b>Number of Flutes</b>	2	<b>Finish</b>	Bright
<b>Flute Style</b>	Spiral flute	<b>For Use On</b>	Stainless steel, iron and steel
<b>Tap Limit</b>	D4	<b>Application</b>	Thread making

## Agency Approvals

<b>UL Listed File #</b>	N/A
<b>UL Recognized File #</b>	N/A
<b>UL Hazardous File #</b>	N/A
<b>CE</b>	None
<b>CSA File #</b>	N/A
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>