

60461 Cut Sheet

Viking machine tap, 9/16-12 UNC, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/60461>

Technical Specifications

Brand	Viking
Item	Machine tap
Thread	9/16-12 UNC
Number of Flutes	3
Flute Style	Spiral flute
Tap Limit	H3

Overall Length	3.5in (89mm)
Tap Drill Size	31/64in
Material	High-speed steel (HSS)
Finish	Bright
For Use On	Stainless steel, iron and steel
Application	Thread making

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement