

68721 Cut Sheet

Viking machine tap, M20 X 2.50 UNC, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/68721>

Technical Specifications

Brand	Viking
Item	Machine tap
Thread	M20 X 2.50 UNC
Number of Flutes	3
Flute Style	Spiral flute
Tap Limit	D7

Overall Length	4.5in (114mm)
Tap Drill Size	17.5mm
Material	High-speed steel (HSS)
Finish	Bright
For Use On	Stainless steel, iron and steel
Application	Thread making

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement