

# 018729-30 Cut Sheet



Stego Filter Fan Plus FPI intake fan, side mount, 120 CFM, 115 VAC operating voltage, G3 (coarse) filter mat, NEMA 12, indoor use only, 6.93 x 6.93in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018729-30>

## Technical Specifications

|   |                        |
|---|------------------------|
| <b>Brand</b>                            | Stego                  |
| <b>Series</b>                           | Filter Fan Plus FPI    |
| <b>Airflow Direction</b>                | Intake                 |
| <b>Item</b>                             | Fan                    |
| <b>Mounting</b>                         | Side                   |
| <b>With Air Flaps</b>                   | No                     |
| <b>Filter Media</b>                     | G3 (coarse) filter mat |
| <b>Free Airflow</b>                     | 120 CFM                |
| <b>Airflow with Grill and Filter(s)</b> | 110 CFM                |
| <b>Operating Voltage</b>                | 115 VAC                |
| <b>Frequency</b>                        | 60 Hz                  |
| <b>Power Consumption</b>                | 38W                    |
| <b>Current Draw</b>                     | 330 mA                 |

|                                |  |
|--------------------------------|--|
| <b>Electrical Connection</b>   | 3-pole clamp for AWG 14 wire, 7.1 in-lb maximum clamping torque  |
| <b>Maximum Static Pressure</b> | 121Pa  |
| <b>Operating Temperature</b>   | -13 to 158 deg F   |
| <b>Average Noise Level</b>     | 58 dBA   |
| <b>NEMA Rating</b>             | 12   |
| <b>Application</b>             | Indoor use only  |
| <b>IP Rating</b>               | IP54   |
| <b>Enclosure Cutout</b>        | 6.93 x 6.93in  |
| <b>Color</b>                   | RAL 7035 light gray  |
| <b>Includes</b>                | Optional mounting screws   |
| <b>Additional Information</b>  | Purchase exhaust grille separately. Fan will also safely operate at 50Hz, but with reduced airflow. Contact manufacturer for 50Hz performance data |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E234324                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |