

# 025410-00 Cut Sheet



Stego LED enclosure light, 100–240 VAC operating voltage, motion sensor switch, 13.8in length, 400 lm, magnet mount, 2-pole plug with snap lock, 5W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/025410-00>

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	LED enclosure light
<b>Operating Voltage</b>	100–240 VAC
<b>Switch Type</b>	Motion sensor
<b>Length</b>	13.8in
<b>Luminous Flux</b>	400 lm
<b>Color Temperature</b>	6000–7000K
<b>Beam Angle</b>	120 degrees

<b>Integral Receptacle</b>	No
<b>Mounting</b>	Magnet
<b>Connection</b>	2-pole plug with snap lock
<b>Power Consumption</b>	5W
<b>IP Rating</b>	IP20
<b>Rotatable</b>	No
<b>Requires</b>	Power or extension cable

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/025410-00.pdf>  
See store item page for other formats.