

852-1328 Cut Sheet



WAGO industrial lean managed Ethernet switch, MAC Security, 8 ports, (6) Ethernet Gigabit (RJ45) and (2) SFP combo Gigabit port(s), Modbus TCP and SNMP, -20 to +70 deg C, metal housing, IP30, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/852-1328>

Technical Specifications

Brand	WAGO
Item	Ethernet switch
Grade	Industrial
Switch Type	Lean managed
Number of Ports	8
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (6) Ethernet Gigabit (RJ45)• (2) SFP combo Gigabit
Communication Standard(s)	<ul style="list-style-type: none">• IEEE 802.3 10Base-T• IEEE 802.3u 100Base-TX/FX• IEEE 802.3ab 1000Base-T• IEEE 802.3x Flow Control• IEEE 802.1p QoS/CoS• IEEE 802.1x Port Authentication• IEEE 802.1q VLAN Tagging• IEEE 802.1AE MAC Security

Port Protocol(s)	<ul style="list-style-type: none">• Modbus TCP• SNMP• webserver (secure HTTPs)
Port Speed(s)	10/100/1000 Mbps auto-detect
Redundant Input Power	Yes
Nominal Input Voltage	9-48 VDC
Operating Temperature	-20 to +70 deg C
Housing Material	Metal
IP Rating	IP30
Mounting	35mm DIN rail
Additional Information	Optional SFP modules sold separately
Programming Software	None, configure via Internet browser

Agency Approvals

UL Listed File #	E482462
UL Recognized File #	NA
UL Hazardous File #	NA
CE	View CE declarations
CSA File #	NA
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/852-1328.pdf>
See store item page for other formats.