


# 9147-10-99-10S Cut Sheet



STAHL ISpac intrinsically safe vibration transducer output isolator, 0.001 Hz to 20 kHz input, 0.001 Hz to 20 kHz output, 24 VDC operating voltage, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9147-10-99-10S>

## Technical Specifications

<b>Brand</b>	STAHL
<b>Series</b>	ISpac
<b>Item</b>	Isolator
<b>Isolator Type</b>	Vibration transducer output
<b>Intrinsically Safe</b>	Yes
<b>Input</b>	0.001 Hz to 20 kHz
<b>Output</b>	0.001 Hz to 20 kHz
<b>Maximum Voltage</b>	26.3 VDC

<b>Maximum Current</b>	88.3 mA
<b>Maximum Power</b>	579 mW
<b>Operating Voltage</b>	24 VDC
<b>Housing Material</b>	Polyamide
<b>Mounting</b>	35mm DIN rail
<b>Connection</b>	Screw terminals
<b>Application</b>	Hazardous location rated

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">View FM Approval and Control Drawing</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/9147-10-99-10S.pdf>  
See store item page for other formats.