

9170-11-13-21S Cut Sheet



STAHL ISpac intrinsically safe digital input isolator, NAMUR sensor or dry contact input, (2) SPDT relay output, 110-230 VAC operating voltage, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9170-11-13-21S>

Technical Specifications

Brand	STAHL	Maximum Current	10 mA
Series	ISpac	Maximum Power	24 mW
Item	Isolator	Operating Voltage	110-230 VAC
Isolator Type	Digital input	Housing Material	Polyamide
Intrinsically Safe	Yes	Mounting	35mm DIN rail
Input	NAMUR sensor or dry contact	Connection	Screw terminals
Output	(2) SPDT relay	Application	Hazardous location rated
Maximum Voltage	9.6 VDC	Manufacturer Part Number	9170/11-13-21s

Agency Approvals

UL Listed File #	E81680
UL Recognized File #	None
UL Hazardous File #	E81680
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	FM Approval and UL Control Drawing

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/9170-11-13-21S.pdf>
See store item page for other formats.