

# 9175-20-14-11S Cut Sheet



STAHL intrinsically safe digital output isolator, (2) 15-31.2 VDC input, (2) 43 mA at 12 VDC output, 24 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9175-20-14-11S>

## Technical Specifications

<b>Brand</b>	STAHL
<b>Item</b>	Isolator
<b>Isolator Type</b>	Digital output
<b>Intrinsically Safe</b>	Yes
<b>Input</b>	(2) 15-31.2 VDC
<b>Output</b>	(2) 43 mA at 12 VDC
<b>Maximum Voltage</b>	19.6 VDC
<b>Maximum Current</b>	150 mA
<b>Maximum Power</b>	732 mW
<b>Operating Voltage</b>	24 VDC
<b>Housing Material</b>	Polyamide
<b>Mounting</b>	35mm DIN rail
<b>Connection</b>	Screw terminals
<b>Application</b>	Hazardous location rated
<b>Additional Information</b>	Manufacturer part number: 9175/20-14-11s

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	E81680
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">View FM Approval and UL Control Drawing</a>