

# 114-10030 Cut Sheet



Sumitomo O2B2 heat shrink tubing, 1/2in trade size, 2:1 shrink ratio, dual wall, hot melt adhesive, flexible, black, flame retardant, 4ft stick length. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/114-10030>

## Technical Specifications

<b>Brand</b>	Sumitomo
<b>Series</b>	O2B2
<b>Item</b>	Heat shrink tubing
<b>Trade Size</b>	1/2in
<b>Shrink Ratio</b>	2:1
<b>Flexibility</b>	Flexible
<b>Wall Type</b>	Dual wall
<b>Outer Wall Material</b>	Irradiated cross-linked polyolefin
<b>Inner Wall Material</b>	Hot melt adhesive
<b>Color</b>	Black
<b>Voltage Rating</b>	600V
<b>Supplied Inside Diameter</b>	0.5in (12.7 mm)
<b>Recovered Inside Diameter</b>	0.25in (6.4 mm)

<b>Recovered Wall Thickness</b>	0.03in (0.75 mm)
<b>Recovered Adhesive Wall Thickness</b>	Thin
<b>Dielectric Strength</b>	1044 V/mil (41.1 kV/mm)
<b>Shrink Temperature</b>	230 °F (110 °C)
<b>Minimum Temperature</b>	-67 °F (-55 °C)
<b>Maximum Temperature</b>	257 °F (125 °C)
<b>Flame Retardant</b>	Yes
<b>Length</b>	4ft stick
<b>Quantity per Pack</b>	5
<b>Applicable Standards</b>	UL 224, CSA C22.2 No. 198.1 and SAE-AS23053/4 Class 2
<b>Application</b>	Damp locations

## Agency Approvals

<b>UL Recognized File #</b>	E75077
<b>CSA File #</b>	LR33298
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>