

115-10079 Cut Sheet

Sumitomo W3B2 heat shrink tubing, 1/2in trade size, 3:1 shrink ratio, dual wall, hot melt adhesive, flexible, black, flame retardant, 4ft stick length. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/115-10079>



Technical Specifications

Brand	Sumitomo	Recovered Wall Thickness	0.071in (1.8 mm)
Series	W3B2	Recovered Adhesive Wall Thickness	Thick
Item	Heat shrink tubing	Dielectric Strength	1044 V/mil (41.1 kV/mm)
Trade Size	1/2in	Shrink Temperature	230 °F (110 °C)
Shrink Ratio	3:1	Minimum Temperature	-67 °F (-55 °C)
Flexibility	Flexible	Maximum Temperature	257 °F (125 °C)
Wall Type	Dual wall	Flame Retardant	Yes
Outer Wall Material	Irradiated cross-linked polyolefin	Length	4ft stick
Inner Wall Material	Hot melt adhesive	Quantity per Pack	5
Color	Black	Applicable Standards	UL 224, CSA C22.2 No. 198.1 and SAE-AS23053/4 Class 3
Voltage Rating	600V	Application	Wet locations
Supplied Inside Diameter	0.5in (12.7 mm)		
Recovered Inside Diameter	0.157in (4 mm)		

Agency Approvals

UL Recognized File #	E75077
CSA File #	LR33298
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement