

A1060804-1 Cut Sheet



LUTZE DRIVEFLEX VFD cable, 4 conductors (includes ground), 8 AWG, 168-stranded, tinned copper, XLPE conductor insulation material, XHHW-2 jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A1060804-1>

Technical Specifications

Brand	LUTZE	Conductor Insulation Color	Black with white numbers and green/yellow ground
Item	Cable	Shielding	Overall foil and braid shielded
Series	DRIVEFLEX	Jacket Material	XHHW-2
Wire/Cable Type	VFD	Jacket Color	Black
UL Wire/Cable Type	TC-ER-JP and WTTTC	Nominal Overall Cable Diameter	0.81in
Applicable Standards	UL 1277	Bulk Length	Cut to length
Application	Drive and motor	Package Type	1 to 50ft = Coil, 51 to 80ft = 14 x 7in Reel, 81 to 130ft = 14 x 10in Reel, 131 to 180ft = 16 x 10in Reel, 181 to 240ft = 18 x 10in Reel, 241 to 510ft = 18 x 13in Reel, 511 to 850ft = 24 x 17in Wooden Reel, 851 to Max = Large Wooden Reel
Flexibility	Semi-flexible		
Voltage Rating	600V (Type TC-ER-JP), 1000V (Type WTTTC, Flexible Motor Supply Cable)		
Conductors	4 conductors (includes ground)		
Conductor Size	8 AWG		
Conductor Stranding	168-stranded		
Conductor Material	Tinned copper		
Conductor Insulation Material	XLPE		

Agency Approvals

UL Listed File #	E352875
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement