

130599-00 Cut Sheet



Stego enclosure heater, axial fan, 950W heating capacity, high performance cartridge heating element, 120 VAC operating voltage, 50/60 Hz, adjustable thermostat, N.C. (open on rise) 32 to 140 deg F, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/130599-00>

Technical Specifications

Brand	Stego
Item	Enclosure heater
IP Rating	IP20
Fan Type	Axial
Heating Capacity	950W
Heating Element	High performance cartridge
Operating Voltage	120 VAC
Hertz	50/60 Hz
Connection	2-pole terminal for 16 AWG max solid or stranded wire
Heater Control	Adjustable thermostat
Contact 1	N.C. (open on rise) 32 to 140 deg F
Switching Differential	7K
Switching Tolerance	+/-4K
Mounting	35mm DIN rail or panel

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document