

A60NF-MXL025-B0250 Cut Sheet



Sung-II Machinery timing pulley, aluminum, 0.08in MXL pitch, 60 tooth, 1.528in pitch diameter, 1/4in bore, hub without flanges. For use with 1/4in wide belt.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A60NF-MXL025-B0250>

Technical Specifications

Brand	Sung-II Machinery
Item	Timing pulley
Material	Aluminum
Pitch	0.08in MXL
Number of Teeth	60
Pitch Diameter	1.528in
Bore Diameter	1/4in
Maximum Allowable Bore	5/8in
Pulley Type	Hub without flanges
Mounting Type	Smooth bore with set screws
For Use With	1/4in wide belt

Agency Approvals

UL Listed File #	Not Applicable
UL Recognized File #	Not Applicable
UL Hazardous File #	Not Applicable
CE	None
CSA File #	Not Applicable
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/A60NF-MXL025-B0250.pdf>
See store item page for other formats.