

1502-6220 Cut Sheet



ASO Safety Solutions safety contact edge, 25 x 30mm, 2ft length. Single sided sealing lip and aluminum mounting rail included. Purchase required end caps separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1502-6220>

Technical Specifications

Brand	ASO Safety Solutions
Item	Safety contact edge
Size	25 x 30mm
Length	2ft
Actuation Force	54.3N
Switching Cycles	>30,000 cycles
Operating Voltage	24 VAC/VDC
Contact Surface Material	TPE
Operating Temperature	-10 to 50C
Includes	Single sided sealing lip and aluminum mounting rail
Additional Information	Purchase required end caps separately

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	E341185
UL Hazardous File #	N/A
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/1502-6220.pdf>
See store item page for other formats.