

151-29227 Cut Sheet

Shaviv deburring blade, E300, for deburring cross-hole both edges, rotating blade, right hand, TiN coated high-speed steel (HSS), long shank. Package of 10. For use with blade holder for E blades and universal deburring tool handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/151-29227>

Technical Specifications

Brand	Shaviv
Item	Deburring blade
Deburring Blade Manufacturer Number	E300
Blade Type	Rotating
Cutting Direction	Right hand
Material	TiN coated high-speed steel (HSS)
Shank	Long shank

Regrindable	No
For Use On	Steel, aluminum, copper, stainless steel and plastic
For Deburring	Cross-hole both edges
Quantity per Pack	10
For Use With	Blade holder for E blades and universal deburring tool handle

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement