

151134 Cut Sheet



FATH swivel caster, silver/gray, thermoplastic polyurethane/nylon/steel. For use with 1.5 x 1.5in, 40 x 40mm and 45 x 45mm T-slotted rails. Double brake included. Requires FATH 151136 or 151261 swivel caster adapter plate.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/151134>

Technical Specifications

Brand	FATH
Item	Swivel caster
Series	15 Series, 40 Series and 45 Series
Color	Silver/gray
Material	Thermoplastic polyurethane/nylon/steel
Load Rating	269 lb/122 kg
For Use With	1.5 x 1.5in, 40 x 40mm and 45 x 45mm T-slotted rails
Includes	Double brake
Requires	FATH 151136 or 151261 swivel caster adapter plate
Manufacturer Part Number	098S100UDN

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement